

# Simple, robust magnetic ballast

## HID-High Power ballasts for MH lamps

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Benefits

- Limited volume of ballast coil; also lightweight
- Simple installation and cabling

### Features

- Orthocyclic winding process
- Ballasts equipped with screw terminal blocks as standard
- Earthing-while-mounting facility (HID Standard ballasts)
- Low watt losses

### Application


- For use with MHN lamps in sports, public, area and floodlighting
- HID-Basic ballasts should be restricted to built-in situations where relative humidity is limited.

# HID-High Power ballasts for MH lamps

## Versions



## Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 2000L 2050	7 mm	102.0 mm	234 mm	185.5 mm	120.0 mm

