



# LuxSpace 2 recessed – high efficiency, visual comfort and a stylish design

## LuxSpace, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

# LuxSpace, recessed

## Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Light color: 830, 840, 930 and 827
- Rim colors: high-gloss metalized, white (RAL9010), grey, black (RAL9005) as standard (any other RAL color possible upon request)
- Rimless version available (not for LED40S versions)
- Surface-mounted version available (not for LED40S versions)
- Compliant for central emergency lighting with DC
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring

## Application

- Halls, offices, conference rooms
- Retail
- Hospitals
- Hotels
- Airports
- Museum





## Specifications

<b>Type</b>	DN570B (low-height recessed version) DN571B (deep-recessed version)
<b>Ceiling type</b>	Plaster (board) ceiling
<b>Light source</b>	Non-replaceable LED module
<b>Power</b>	12.6, 21, 25.5, 36 W (3,000 K) 12.6, 19.8, 24, 36 W (4000K)
<b>Light colour:</b>	830, 840, 930 and 827
<b>Luminous flux (for 830 and 840 versions)</b>	DN570B, high-gloss mirror or faceted reflector: 1,350, 2,200, 2,600, 4,000 lm DN570B, matt reflector: 1,150, 1,850, 2,200, 4,000 lm DN570B, white reflector: 1,300, 2,100, 2,500, 4,000 lm DN571B, high-gloss mirror or faceted reflector: 1,300, 2,100, 2,500, 4,000 lm DN571B, matt reflector: 1,000, 1,650, 1,950, 4,000 lm DN571B, white reflector: 1,250, 2,000, 2,400, 4,000 lm
<b>Colour Rendering Index</b>	> 80
<b>Lumen maintenance at median useful life* 50,000 h</b>	L90
<b>Control gear failure rate at median useful life 50,000 h</b>	5%
<b>Performance Ambient Temperature Tq</b>	+25 °C

<b>Operating temperature range</b>	+10 to +40 °C
<b>Driver</b>	Separate
<b>Mains voltage</b>	230 or 240 V/50-60 Hz
<b>Dimming</b>	DALI dimming possible (PSED-E)
<b>Options</b>	Emergency lighting 3 hours (EL3) Protection glass (PG or PGO, IP54 front face) Through-wiring Rimless version for plaster ceiling (not for LED40S) Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR) External or plug-in 3-pole Wieland/Adels connector
<b>Material</b>	Housing and rim: aluminium Reflector: plastic, aluminium-coated (for high-gloss and faceted optics)
<b>Colour</b>	Rim: white (RAL 9010), grey, black (RAL 9005) or high-gloss metalised
<b>Optic</b>	High-gloss mirror (C) Matt mirror (M) Faceted reflector (F) White reflector (WR)
<b>Connection</b>	Push-in connector or with pull relief
<b>Installation</b>	Fixed with spring fasteners
<b>Remarks</b>	External driver included

# LuxSpace, recessed

## Versions



## Product details



## Accessories

Protection glass

Ordercode 93234500

Protection glass, opal

Ordercode 93235200



### Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

### Approval and Application

Mech. impact protection code	IK02
------------------------------	------

### Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

### General Information

Cap-Base	-
CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
Flammability mark	F
Gear	-
Glow-wire test	Temperature 850 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit
UL mark	No

### Initial Performance (IEC Compliant)

Init. Colour Rendering Index	>80
Luminous flux tolerance	+/-10%

### Mechanical and Housing

Colour	White RAL 9003
--------	----------------

### Application Conditions

Order Code	Full Product Name	Maximum dim level
93042600	DN570B LED12S/830 PSD-VLC-E C WH	1%
93043300	DN570B LED12S/840 PSD-VLC-E C WH	1%
93052500	DN570B LED20S/830 PSU-E C WH	-
93053200	DN570B LED20S/840 PSU-E C WH	-
93054900	DN570B LED20S/830 PSD-VLC-E C WH	1%
93076100	DN570B LED20S/830 PSU-E C PG WH	-
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	1%
93080800	DN570B LED24S/830 PSU-E C WH	-
93081500	DN570B LED24S/840 PSU-E C WH	-
93082200	DN570B LED24S/830 PSD-VLC-E C WH	1%
93083900	DN570B LED24S/840 PSD-VLC-E C WH	1%
93102700	DN570B LED20S/830 PSU-E C WH SG-O	-
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	-
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	-
94120000	DN570B LED40S/830 PSU-E C WH	-
94121700	DN570B LED40S/840 PSU-E C WH	-
94122400	DN570B LED40S/830 PSD-VLC-E C WH	1%
94123100	DN570B LED40S/840 PSD-VLC-E C WH	1%
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	-
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	-
93044000	DN570B LED12S/830 PSU-E F WH	-
93045700	DN570B LED12S/840 PSU-E F WH	-
93046400	DN570B LED12S/830 PSED-VLC-E F WH	1%
93047100	DN570B LED12S/840 PSD-VLC-E F WH	1%
93056300	DN570B LED20S/830 PSU-E F WH	-
93057000	DN570B LED20S/840 PSU-E F WH	-
93058700	DN570B LED20S/830 PSD-VLC-E F WH	1%
93059400	DN570B LED20S/840 PSD-VLC-E F WH	1%
93078500	DN570B LED20S/830 PSU-E F PG WH	-
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	1%
93084600	DN570B LED24S/830 PSU-E F WH	-
93085300	DN570B LED24S/840 PSU-E F WH	-
93086000	DN570B LED24S/830 PSD-VLC-E F WH	1%
93087700	DN570B LED24S/840 PSD-VLC-E F WH	1%
94124800	DN570B LED40S/830 PSU-E F WH	-
94125500	DN570B LED40S/840 PSU-E F WH	-
94127900	DN570B LED40S/840 PSD-VLC-E F WH	1%

Order Code	Full Product Name	Maximum dim level
93048800	DN570B LED12S/830 PSU-E M WH	-
93049500	DN570B LED12S/830 PSED-VLC-E M WH	1%
93060000	DN570B LED20S/830 PSU-E M WH	-
93061700	DN570B LED20S/830 PSD-VLC-E M WH	1%
93050100	DN570B LED12S/830 PSE-E WR WH	-
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	1%
93062400	DN570B LED20S/830 PSU-E WR WH	-
93105800	DN571B LED12S/830 PSU-E C WH	-
93106500	DN571B LED12S/840 PSU-E C WH	-
93107200	DN571B LED12S/830 PSD-VLC-E C WH	1%
93117100	DN571B LED20S/830 PSU-E C WH	-
93118800	DN571B LED20S/840 PSU-E C WH	-
93119500	DN571B LED20S/830 PSD-VLC-E C WH	1%
93120100	DN571B LED20S/840 PSD-VLC-E C WH	1%
93141600	DN571B LED20S/830 PSU-E C PG WH	-
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	1%
93145400	DN571B LED24S/830 PSE-E C WH	-
93146100	DN571B LED24S/840 PSE-E C WH	-
93147800	DN571B LED24S/830 PSED-VLC-E C WH	1%
93148500	DN571B LED24S/840 PSED-VLC-E C WH	1%
94128600	DN571B LED40S/830 PSE-E C WH	-
94129300	DN571B LED40S/840 PSE-E C WH	-
94130900	DN571B LED40S/830 PSED-VLC-E C WH	1%
94131600	DN571B LED40S/840 PSED-VLC-E C WH	1%
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	-
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	1% (no dimming in emergency mode)
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	-
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	1% (no dimming in emergency mode)
93109600	DN571B LED12S/830 PSE-E F WH	-
93110200	DN571B LED12S/840 PSU-E F WH	-
93112600	DN571B LED12S/840 PSD-VLC-E F WH	1%
93121800	DN571B LED20S/830 PSU-E F WH	-
93122500	DN571B LED20S/840 PSU-E F WH	-
93123200	DN571B LED20S/830 PSD-VLC-E F WH	1%
93124900	DN571B LED20S/840 PSD-VLC-E F WH	1%
93149200	DN571B LED24S/830 PSE-E F WH	-
93150800	DN571B LED24S/840 PSE-E F WH	-
93151500	DN571B LED24S/830 PSED-VLC-E F WH	1%
93152200	DN571B LED24S/840 PSED-VLC-E F WH	1%
94132300	DN571B LED40S/830 PSE-E F WH	-
94133000	DN571B LED40S/840 PSE-E F WH	-
94134700	DN571B LED40S/830 PSED-VLC-E F WH	1%
94135400	DN571B LED40S/840 PSED-VLC-E F WH	1%
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	1%
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	1%
93126300	DN571B LED20S/830 PSD-VLC-E M WH	1%

### Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
93042600	DN570B LED12S/830 PSD-VLC-E C WH	IP20	93052500	DN570B LED20S/830 PSU-E C WH	IP20
93043300	DN570B LED12S/840 PSD-VLC-E C WH	IP20	93053200	DN570B LED20S/840 PSU-E C WH	IP20

Order Code	Full Product Name	Ingress protection code
93054900	DN570B LED20S/830 PSD-VLC-E C WH	IP20
93076100	DN570B LED20S/830 PSU-E C PG WH	IP20/54
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	IP20/54
93080800	DN570B LED24S/830 PSU-E C WH	IP20
93081500	DN570B LED24S/840 PSU-E C WH	IP20
93082200	DN570B LED24S/830 PSD-VLC-E C WH	IP20
93083900	DN570B LED24S/840 PSD-VLC-E C WH	IP20
93102700	DN570B LED20S/830 PSU-E C WH SG-O	IP20
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	IP20
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	IP20
94120000	DN570B LED40S/830 PSU-E C WH	IP20
94121700	DN570B LED40S/840 PSU-E C WH	IP20
94122400	DN570B LED40S/830 PSD-VLC-E C WH	IP20
94123100	DN570B LED40S/840 PSD-VLC-E C WH	IP20
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	IP20
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	IP20
93044000	DN570B LED12S/830 PSU-E F WH	IP20
93045700	DN570B LED12S/840 PSU-E F WH	IP20
93046400	DN570B LED12S/830 PSED-VLC-E F WH	IP20
93047100	DN570B LED12S/840 PSD-VLC-E F WH	IP20
93056300	DN570B LED20S/830 PSU-E F WH	IP20
93057000	DN570B LED20S/840 PSU-E F WH	IP20
93058700	DN570B LED20S/830 PSD-VLC-E F WH	IP20
93059400	DN570B LED20S/840 PSD-VLC-E F WH	IP20
93078500	DN570B LED20S/830 PSU-E F PG WH	IP20/54
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	IP20/54
93084600	DN570B LED24S/830 PSU-E F WH	IP20
93085300	DN570B LED24S/840 PSU-E F WH	IP20
93086000	DN570B LED24S/830 PSD-VLC-E F WH	IP20
93087700	DN570B LED24S/840 PSD-VLC-E F WH	IP20
94124800	DN570B LED40S/830 PSU-E F WH	IP20
94125500	DN570B LED40S/840 PSU-E F WH	IP20
94127900	DN570B LED40S/840 PSD-VLC-E F WH	IP20
93048800	DN570B LED12S/830 PSU-E M WH	IP20
93049500	DN570B LED12S/830 PSED-VLC-E M WH	IP20
93060000	DN570B LED20S/830 PSU-E M WH	IP20
93061700	DN570B LED20S/830 PSD-VLC-E M WH	IP20
93050100	DN570B LED12S/830 PSE-E WR WH	IP20
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	IP20
93062400	DN570B LED20S/830 PSU-E WR WH	IP20

Order Code	Full Product Name	Ingress protection code
93105800	DN571B LED12S/830 PSU-E C WH	IP20
93106500	DN571B LED12S/840 PSU-E C WH	IP20
93107200	DN571B LED12S/830 PSD-VLC-E C WH	IP20
93117100	DN571B LED20S/830 PSU-E C WH	IP20
93118800	DN571B LED20S/840 PSU-E C WH	IP20
93119500	DN571B LED20S/830 PSD-VLC-E C WH	IP20
93120100	DN571B LED20S/840 PSD-VLC-E C WH	IP20
93141600	DN571B LED20S/830 PSU-E C PG WH	IP20/54
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	IP20/54
93145400	DN571B LED24S/830 PSE-E C WH	IP20
93146100	DN571B LED24S/840 PSE-E C WH	IP20
93147800	DN571B LED24S/830 PSED-VLC-E C WH	IP20
93148500	DN571B LED24S/840 PSED-VLC-E C WH	IP20
94128600	DN571B LED40S/830 PSE-E C WH	IP20
94129300	DN571B LED40S/840 PSE-E C WH	IP20
94130900	DN571B LED40S/830 PSED-VLC-E C WH	IP20
94131600	DN571B LED40S/840 PSED-VLC-E C WH	IP20
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	IP20
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	IP20
93109600	DN571B LED12S/830 PSE-E F WH	IP20
93110200	DN571B LED12S/840 PSU-E F WH	IP20
93112600	DN571B LED12S/840 PSD-VLC-E F WH	IP20
93121800	DN571B LED20S/830 PSU-E F WH	IP20
93122500	DN571B LED20S/840 PSU-E F WH	IP20
93123200	DN571B LED20S/830 PSD-VLC-E F WH	IP20
93124900	DN571B LED20S/840 PSD-VLC-E F WH	IP20
93149200	DN571B LED24S/830 PSE-E F WH	IP20
93150800	DN571B LED24S/840 PSE-E F WH	IP20
93151500	DN571B LED24S/830 PSED-VLC-E F WH	IP20
93152200	DN571B LED24S/840 PSED-VLC-E F WH	IP20
94132300	DN571B LED40S/830 PSE-E F WH	IP20
94133000	DN571B LED40S/840 PSE-E F WH	IP20
94134700	DN571B LED40S/830 PSED-VLC-E F WH	IP20
94135400	DN571B LED40S/840 PSED-VLC-E F WH	IP20
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	IP20
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	IP20
93126300	DN571B LED20S/830 PSD-VLC-E M WH	IP20

**Controls and Dimming**

Order Code	Full Product Name	Dimmable
93042600	DN570B LED12S/830 PSD-VLC-E C WH	Yes
93043300	DN570B LED12S/840 PSD-VLC-E C WH	Yes
93052500	DN570B LED20S/830 PSU-E C WH	No
93053200	DN570B LED20S/840 PSU-E C WH	No
93054900	DN570B LED20S/830 PSD-VLC-E C WH	Yes
93076100	DN570B LED20S/830 PSU-E C PG WH	No
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	Yes
93080800	DN570B LED24S/830 PSU-E C WH	No

Order Code	Full Product Name	Dimmable
93081500	DN570B LED24S/840 PSU-E C WH	No
93082200	DN570B LED24S/830 PSD-VLC-E C WH	Yes
93083900	DN570B LED24S/840 PSD-VLC-E C WH	Yes
93102700	DN570B LED20S/830 PSU-E C WH SG-O	No
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	No
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	No
94120000	DN570B LED40S/830 PSU-E C WH	No
94121700	DN570B LED40S/840 PSU-E C WH	No

## LuxSpace, recessed

Order Code	Full Product Name	Dimmable
94122400	DN570B LED40S/830 PSD-VLC-E C WH	Yes
94123100	DN570B LED40S/840 PSD-VLC-E C WH	Yes
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	No
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	No
93044000	DN570B LED12S/830 PSU-E F WH	No
93045700	DN570B LED12S/840 PSU-E F WH	No
93046400	DN570B LED12S/830 PSED-VLC-E F WH	Yes
93047100	DN570B LED12S/840 PSD-VLC-E F WH	Yes
93056300	DN570B LED20S/830 PSU-E F WH	No
93057000	DN570B LED20S/840 PSU-E F WH	No
93058700	DN570B LED20S/830 PSD-VLC-E F WH	Yes
93059400	DN570B LED20S/840 PSD-VLC-E F WH	Yes
93078500	DN570B LED20S/830 PSU-E F PG WH	No
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	Yes
93084600	DN570B LED24S/830 PSU-E F WH	No
93085300	DN570B LED24S/840 PSU-E F WH	No
93086000	DN570B LED24S/830 PSD-VLC-E F WH	Yes
93087700	DN570B LED24S/840 PSD-VLC-E F WH	Yes
94124800	DN570B LED40S/830 PSU-E F WH	No
94125500	DN570B LED40S/840 PSU-E F WH	No
94127900	DN570B LED40S/840 PSD-VLC-E F WH	Yes
93048800	DN570B LED12S/830 PSU-E M WH	No
93049500	DN570B LED12S/830 PSED-VLC-E M WH	Yes
93060000	DN570B LED20S/830 PSU-E M WH	No
93061700	DN570B LED20S/830 PSD-VLC-E M WH	Yes
93050100	DN570B LED12S/830 PSE-E WR WH	No
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	Yes
93062400	DN570B LED20S/830 PSU-E WR WH	No
93105800	DN571B LED12S/830 PSU-E C WH	No
93106500	DN571B LED12S/840 PSU-E C WH	No
93107200	DN571B LED12S/830 PSD-VLC-E C WH	Yes
93117100	DN571B LED20S/830 PSU-E C WH	No
93118800	DN571B LED20S/840 PSU-E C WH	No
93119500	DN571B LED20S/830 PSD-VLC-E C WH	Yes

Order Code	Full Product Name	Dimmable
93120100	DN571B LED20S/840 PSD-VLC-E C WH	Yes
93141600	DN571B LED20S/830 PSU-E C PG WH	No
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	Yes
93145400	DN571B LED24S/830 PSE-E C WH	No
93146100	DN571B LED24S/840 PSE-E C WH	No
93147800	DN571B LED24S/830 PSED-VLC-E C WH	Yes
93148500	DN571B LED24S/840 PSED-VLC-E C WH	Yes
94128600	DN571B LED40S/830 PSE-E C WH	No
94129300	DN571B LED40S/840 PSE-E C WH	No
94130900	DN571B LED40S/830 PSED-VLC-E C WH	Yes
94131600	DN571B LED40S/840 PSED-VLC-E C WH	Yes
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	No
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	Yes
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	No
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	Yes
93109600	DN571B LED12S/830 PSE-E F WH	No
93110200	DN571B LED12S/840 PSU-E F WH	No
93112600	DN571B LED12S/840 PSD-VLC-E F WH	Yes
93121800	DN571B LED20S/830 PSU-E F WH	No
93122500	DN571B LED20S/840 PSU-E F WH	No
93123200	DN571B LED20S/830 PSD-VLC-E F WH	Yes
93124900	DN571B LED20S/840 PSD-VLC-E F WH	Yes
93149200	DN571B LED24S/830 PSE-E F WH	No
93150800	DN571B LED24S/840 PSE-E F WH	No
93151500	DN571B LED24S/830 PSED-VLC-E F WH	Yes
93152200	DN571B LED24S/840 PSED-VLC-E F WH	Yes
94132300	DN571B LED40S/830 PSE-E F WH	No
94133000	DN571B LED40S/840 PSE-E F WH	No
94134700	DN571B LED40S/830 PSED-VLC-E F WH	Yes
94135400	DN571B LED40S/840 PSED-VLC-E F WH	Yes
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	Yes
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	Yes
93126300	DN571B LED20S/830 PSD-VLC-E M WH	Yes

### General Information (1/2)

Order Code	Full Product Name	Optical			
		cover/ lens type	Decorative accessories	Emergency lighting	ENEC mark
93042600	DN570B LED12S/830 PSD-VLC-E C WH	No	No	No	ENEC mark
93043300	DN570B LED12S/840 PSD-VLC-E C WH	No	No	No	ENEC mark
93052500	DN570B LED20S/830 PSU-E C WH	No	No	No	ENEC mark
93053200	DN570B LED20S/840 PSU-E C WH	No	No	No	ENEC mark
93054900	DN570B LED20S/830 PSD-VLC-E C WH	No	No	No	ENEC mark

Order Code	Full Product Name	Optical			
		cover/ lens type	Decorative accessories	Emergency lighting	ENEC mark
93076100	DN570B LED20S/830 PSU-E C PG WH	PG	No	No	ENEC mark
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	PG	No	No	ENEC mark
93080800	DN570B LED24S/830 PSU-E C WH	No	No	No	ENEC mark
93081500	DN570B LED24S/840 PSU-E C WH	No	No	No	ENEC mark
93082200	DN570B LED24S/830 PSD-VLC-E C WH	No	No	No	ENEC mark

Order Code	Full Product Name	Optical cover/				ENEC mark
		lens type	Decorative accessories	Emergency lighting	Emergency lighting	
93083900	DN570B LED24S/840 PSD-VLC-E C WH	No	No	No	ENE mark	
93102700	DN570B LED20S/830 PSU-E C WH SG-O	No	SG-O	No	ENE mark	
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	No	SG-FRC	No	ENE mark	
93104100	DN570B LED20S/830 PSU-E C WH SG-HR- FR	No	SG-HR-FR	No	ENE mark	
94120000	DN570B LED40S/830 PSU-E C WH	No	No	No	ENE mark	
94121700	DN570B LED40S/840 PSU-E C WH	No	No	No	ENE mark	
94122400	DN570B LED40S/830 PSD-VLC-E C WH	No	No	No	ENE mark	
94123100	DN570B LED40S/840 PSD-VLC-E C WH	No	No	No	ENE mark	
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-	
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-	
93044000	DN570B LED12S/830 PSU-E F WH	No	No	No	ENE mark	
93045700	DN570B LED12S/840 PSU-E F WH	No	No	No	ENE mark	
93046400	DN570B LED12S/830 PSED-VLC-E F WH	No	No	No	ENE mark	
93047100	DN570B LED12S/840 PSD-VLC-E F WH	No	No	No	ENE mark	
93056300	DN570B LED20S/830 PSU-E F WH	No	No	No	ENE mark	
93057000	DN570B LED20S/840 PSU-E F WH	No	No	No	ENE mark	
93058700	DN570B LED20S/830 PSD-VLC-E F WH	No	No	No	ENE mark	
93059400	DN570B LED20S/840 PSD-VLC-E F WH	No	No	No	ENE mark	
93078500	DN570B LED20S/830 PSU-E F PG WH	PG	No	No	ENE mark	
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	PG	No	No	ENE mark	
93084600	DN570B LED24S/830 PSU-E F WH	No	No	No	ENE mark	

Order Code	Full Product Name	Optical cover/				ENEC mark
		lens type	Decorative accessories	Emergency lighting	Emergency lighting	
93085300	DN570B LED24S/840 PSU-E F WH	No	No	No	ENE mark	
93086000	DN570B LED24S/830 PSD-VLC-E F WH	No	No	No	ENE mark	
93087700	DN570B LED24S/840 PSD-VLC-E F WH	No	No	No	ENE mark	
94124800	DN570B LED40S/830 PSU-E F WH	No	No	No	ENE mark	
94125500	DN570B LED40S/840 PSU-E F WH	No	No	No	ENE mark	
94127900	DN570B LED40S/840 PSD-VLC-E F WH	No	No	No	ENE mark	
93048800	DN570B LED12S/830 PSU-E M WH	No	No	No	ENE mark	
93049500	DN570B LED12S/830 PSED-VLC-E M WH	No	No	No	ENE mark	
93060000	DN570B LED20S/830 PSU-E M WH	No	No	No	ENE mark	
93061700	DN570B LED20S/830 PSD-VLC-E M WH	No	No	No	ENE mark	
93050100	DN570B LED12S/830 PSE-E WR WH	No	No	No	ENE mark	
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	No	No	No	ENE mark	
93062400	DN570B LED20S/830 PSU-E WR WH	No	No	No	ENE mark	
93105800	DN571B LED12S/830 PSU-E C WH	No	No	No	ENE mark	
93106500	DN571B LED12S/840 PSU-E C WH	No	No	No	ENE mark	
93107200	DN571B LED12S/830 PSD-VLC-E C WH	No	No	No	ENE mark	
93117100	DN571B LED20S/830 PSU-E C WH	No	No	No	ENE mark	
93118800	DN571B LED20S/840 PSU-E C WH	No	No	No	ENE mark	
93119500	DN571B LED20S/830 PSD-VLC-E C WH	No	No	No	ENE mark	
93120100	DN571B LED20S/840 PSD-VLC-E C WH	No	No	No	ENE mark	
93141600	DN571B LED20S/830 PSU-E C PG WH	PG	No	No	ENE mark	
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	PG	No	No	ENE mark	
93145400	DN571B LED24S/830 PSE-E C WH	No	No	No	ENE mark	
93146100	DN571B LED24S/840 PSE-E C WH	No	No	No	ENE mark	



## LuxSpace, recessed

Order Code	Full Product Name	Optical cover/			
		lens type	Decorative accessories	Emergency lighting	ENEC mark
93147800	DN571B LED24S/830 PSED-VLC-E C WH	No	No	No	ENEC mark
93148500	DN571B LED24S/840 PSED-VLC-E C WH	No	No	No	ENEC mark
94128600	DN571B LED40S/830 PSE-E C WH	No	No	No	ENEC mark
94129300	DN571B LED40S/840 PSE-E C WH	No	No	No	ENEC mark
94130900	DN571B LED40S/830 PSED-VLC-E C WH	No	No	No	ENEC mark
94131600	DN571B LED40S/840 PSED-VLC-E C WH	No	No	No	ENEC mark
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	-	-	Emergency lighting 3 hours duration Pro version	-
93109600	DN571B LED12S/830 PSE-E F WH	No	No	No	ENEC mark

Order Code	Full Product Name	Optical cover/			
		lens type	Decorative accessories	Emergency lighting	ENEC mark
93110200	DN571B LED12S/840 PSU-E F WH	No	No	No	ENEC mark
93112600	DN571B LED12S/840 PSD-VLC-E F WH	No	No	No	ENEC mark
93121800	DN571B LED20S/830 PSU-E F WH	No	No	No	ENEC mark
93122500	DN571B LED20S/840 PSU-E F WH	No	No	No	ENEC mark
93123200	DN571B LED20S/830 PSD-VLC-E F WH	No	No	No	ENEC mark
93124900	DN571B LED20S/840 PSD-VLC-E F WH	No	No	No	ENEC mark
93149200	DN571B LED24S/830 PSE-E F WH	No	No	No	ENEC mark
93150800	DN571B LED24S/840 PSE-E F WH	No	No	No	ENEC mark
93151500	DN571B LED24S/830 PSED-VLC-E F WH	No	No	No	ENEC mark
93152200	DN571B LED24S/840 PSED-VLC-E F WH	No	No	No	ENEC mark
94132300	DN571B LED40S/830 PSE-E F WH	No	No	No	ENEC mark
94133000	DN571B LED40S/840 PSE-E F WH	No	No	No	ENEC mark
94134700	DN571B LED40S/830 PSED-VLC-E F WH	No	No	No	ENEC mark
94135400	DN571B LED40S/840 PSED-VLC-E F WH	No	No	No	ENEC mark
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	No	No	No	ENEC mark
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	No	No	No	ENEC mark
93126300	DN571B LED20S/830 PSD-VLC-E M WH	No	No	No	ENEC mark

### General Information (2/2)

Order Code	Full Product Name	Lamp family code	Number of		Product Family Code
			light sources	Optic type	
93042600	DN570B LED12S/830 PSD-VLC-E C WH	LED12S	1	C	DN570B
93043300	DN570B LED12S/840 PSD-VLC-E C WH	LED12S	1	C	DN570B
93052500	DN570B LED20S/830 PSU-E C WH	LED20S	1	C	DN570B
93053200	DN570B LED20S/840 PSU-E C WH	LED20S	1	C	DN570B

Order Code	Full Product Name	Lamp family code	Number of		Product Family Code
			light sources	Optic type	
93054900	DN570B LED20S/830 PSD-VLC-E C WH	LED20S	1	C	DN570B
93076100	DN570B LED20S/830 PSU-E C PG WH	LED20S	1	C	DN570B
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	LED20S	1	C	DN570B
93080800	DN570B LED24S/830 PSU-E C WH	LED24S	1	C	DN570B

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
93081500	DN570B LED24S/840 PSU-E C WH	LED24S	1	C	DN570B
93082200	DN570B LED24S/830 PSD-VLC-E C WH	LED24S	1	C	DN570B
93083900	DN570B LED24S/840 PSD-VLC-E C WH	LED24S	1	C	DN570B
93102700	DN570B LED20S/830 PSU-E C WH SG-O	LED20S	1	C	DN570B
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	LED20S	1	C	DN570B
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	LED20S	1	C	DN570B
94120000	DN570B LED40S/830 PSU-E C WH	LED40S	1	C	DN570B
94121700	DN570B LED40S/840 PSU-E C WH	LED40S	1	C	DN570B
94122400	DN570B LED40S/830 PSD-VLC-E C WH	LED40S	1	C	DN570B
94123100	DN570B LED40S/840 PSD-VLC-E C WH	LED40S	1	C	DN570B
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	LED20S	-	C	DN570B
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	LED20S	-	C	DN570B
93044000	DN570B LED12S/830 PSU-E F WH	LED12S	1	F	DN570B
93045700	DN570B LED12S/840 PSU-E F WH	LED12S	1	F	DN570B
93046400	DN570B LED12S/830 PSED-VLC-E F WH	LED12S	1	F	DN570B
93047100	DN570B LED12S/840 PSD-VLC-E F WH	LED12S	1	F	DN570B
93056300	DN570B LED20S/830 PSU-E F WH	LED20S	1	F	DN570B
93057000	DN570B LED20S/840 PSU-E F WH	LED20S	1	F	DN570B
93058700	DN570B LED20S/830 PSD-VLC-E F WH	LED20S	1	F	DN570B
93059400	DN570B LED20S/840 PSD-VLC-E F WH	LED20S	1	F	DN570B
93078500	DN570B LED20S/830 PSU-E F PG WH	LED20S	1	F	DN570B
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	LED20S	1	F	DN570B
93084600	DN570B LED24S/830 PSU-E F WH	LED24S	1	F	DN570B
93085300	DN570B LED24S/840 PSU-E F WH	LED24S	1	F	DN570B
93086000	DN570B LED24S/830 PSD-VLC-E F WH	LED24S	1	F	DN570B

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
93087700	DN570B LED24S/840 PSD-VLC-E F WH	LED24S	1	F	DN570B
94124800	DN570B LED40S/830 PSU-E F WH	LED40S	1	F	DN570B
94125500	DN570B LED40S/840 PSU-E F WH	LED40S	1	F	DN570B
94127900	DN570B LED40S/840 PSD-VLC-E F WH	LED40S	1	F	DN570B
93048800	DN570B LED12S/830 PSU-E M WH	LED12S	1	M	DN570B
93049500	DN570B LED12S/830 PSED-VLC-E M WH	LED12S	1	M	DN570B
93060000	DN570B LED20S/830 PSU-E M WH	LED20S	1	M	DN570B
93061700	DN570B LED20S/830 PSD-VLC-E M WH	LED20S	1	M	DN570B
93050100	DN570B LED12S/830 PSE-E WR WH	LED12S	1	WR	DN570B
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	LED12S	1	WR	DN570B
93062400	DN570B LED20S/830 PSU-E WR WH	LED20S	1	WR	DN570B
93105800	DN571B LED12S/830 PSU-E C WH	LED12S	1	C	DN571B
93106500	DN571B LED12S/840 PSU-E C WH	LED12S	1	C	DN571B
93107200	DN571B LED12S/830 PSD-VLC-E C WH	LED12S	1	C	DN571B
93117100	DN571B LED20S/830 PSU-E C WH	LED20S	1	C	DN571B
93118800	DN571B LED20S/840 PSU-E C WH	LED20S	1	C	DN571B
93119500	DN571B LED20S/830 PSD-VLC-E C WH	LED20S	1	C	DN571B
93120100	DN571B LED20S/840 PSD-VLC-E C WH	LED20S	1	C	DN571B
93141600	DN571B LED20S/830 PSU-E C PG WH	LED20S	1	C	DN571B
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	LED20S	1	C	DN571B
93145400	DN571B LED24S/830 PSE-E C WH	LED24S	1	C	DN571B
93146100	DN571B LED24S/840 PSE-E C WH	LED24S	1	C	DN571B
93147800	DN571B LED24S/830 PSED-VLC-E C WH	LED24S	1	C	DN571B
93148500	DN571B LED24S/840 PSED-VLC-E C WH	LED24S	1	C	DN571B
94128600	DN571B LED40S/830 PSE-E C WH	LED40S	1	C	DN571B

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
94129300	DN571B LED40S/840 PSE-E C WH	LED40S	1	C	DN571B
94130900	DN571B LED40S/830 PSED-VLC-E C WH	LED40S	1	C	DN571B
94131600	DN571B LED40S/840 PSED-VLC-E C WH	LED40S	1	C	DN571B
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	LED20S	-	C	DN571B
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	LED20S	-	C	DN571B
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	LED20S	-	C	DN571B
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	LED20S	-	C	DN571B
93109600	DN571B LED12S/830 PSE-E F WH	LED12S	1	F	DN571B
93110200	DN571B LED12S/840 PSU-E F WH	LED12S	1	F	DN571B
93112600	DN571B LED12S/840 PSD-VLC-E F WH	LED12S	1	F	DN571B
93121800	DN571B LED20S/830 PSU-E F WH	LED20S	1	F	DN571B
93122500	DN571B LED20S/840 PSU-E F WH	LED20S	1	F	DN571B
93123200	DN571B LED20S/830 PSD-VLC-E F WH	LED20S	1	F	DN571B

Order Code	Full Product Name	Lamp family code	Number of light sources	Optic type	Product Family Code
93124900	DN571B LED20S/840 PSD-VLC-E F WH	LED20S	1	F	DN571B
93149200	DN571B LED24S/830 PSE-E F WH	LED24S	1	F	DN571B
93150800	DN571B LED24S/840 PSE-E F WH	LED24S	1	F	DN571B
93151500	DN571B LED24S/830 PSED-VLC-E F WH	LED24S	1	F	DN571B
93152200	DN571B LED24S/840 PSED-VLC-E F WH	LED24S	1	F	DN571B
94132300	DN571B LED40S/830 PSE-E F WH	LED40S	1	F	DN571B
94133000	DN571B LED40S/840 PSE-E F WH	LED40S	1	F	DN571B
94134700	DN571B LED40S/830 PSED-VLC-E F WH	LED40S	1	F	DN571B
94135400	DN571B LED40S/840 PSED-VLC-E F WH	LED40S	1	F	DN571B
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	LED12S	1	WR	DN571B
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	LED20S	1	WR	DN571B
93126300	DN571B LED20S/830 PSD-VLC-E M WH	LED20S	1	M	DN571B

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
93042600	DN570B LED12S/830 PSD-VLC-E C WH	(0.43, 0.40)	3000 K	123 lm/W	1350 lm
93043300	DN570B LED12S/840 PSD-VLC-E C WH	(0.38, 0.37)	4000 K	123 lm/W	1350 lm
93052500	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40)	3000 K	116 lm/W	2200 lm
93053200	DN570B LED20S/840 PSU-E C WH	(0.38, 0.37)	4000 K	126 lm/W	2200 lm
93054900	DN570B LED20S/830 PSD-VLC-E C WH	(0.43, 0.40)	3000 K	116 lm/W	2200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
93076100	DN570B LED20S/830 PSU-E C PG WH	(0.43, 0.40)	3000 K	111 lm/W	2100 lm
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	(0.43, 0.40)	3000 K	111 lm/W	2100 lm
93080800	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm
93081500	DN570B LED24S/840 PSU-E C WH	(0.38, 0.37)	4000 K	124 lm/W	2600 lm
93082200	DN570B LED24S/830 PSD-VLC-E C WH	(0.43, 0.40)	3000 K	113 lm/W	2600 lm

## LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
93083900	DN570B LED24S/840 PSD-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	124 lm/W	2600 lm
93102700	DN570B LED20S/830 PSU-E C WH SG-O	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	1800 lm
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	1800 lm
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	1850 lm
94120000	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	124 lm/W	4200 lm
94121700	DN570B LED40S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	131 lm/W	4200 lm
94122400	DN570B LED40S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	124 lm/W	4200 lm
94123100	DN570B LED40S/840 PSD-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	131 lm/W	4200 lm
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM <3	3000 K	100 lm/W	2200 lm
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.37) SDCM <3	4000 K	126 lm/W	2200 lm
93044000	DN570B LED12S/830 PSU-E F WH	(0.43, 0.40) SDCM <3	3000 K	123 lm/W	1350 lm
93045700	DN570B LED12S/840 PSU-E F WH	(0.38, 0.37) SDCM <3	4000 K	123 lm/W	1350 lm
93046400	DN570B LED12S/830 PSED-VLC-E F WH	(0.43, 0.40) SDCM <3	3000 K	123 lm/W	1350 lm
93047100	DN570B LED12S/840	(0.38, 0.37) SDCM <3	4000 K	123 lm/W	1350 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSD-VLC-E F WH				
93056300	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40) SDCM <3	3000 K	116 lm/W	2200 lm
93057000	DN570B LED20S/840 PSU-E F WH	(0.38, 0.37) SDCM <3	4000 K	126 lm/W	2200 lm
93058700	DN570B LED20S/830 PSD-VLC-E F WH	(0.43, 0.40) SDCM <3	3000 K	116 lm/W	2200 lm
93059400	DN570B LED20S/840 PSD-VLC-E F WH	(0.38, 0.37) SDCM <3	4000 K	126 lm/W	2200 lm
93078500	DN570B LED20S/830 PSU-E F PG WH	(0.43, 0.40) SDCM <3	3000 K	111 lm/W	2100 lm
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	(0.43, 0.40) SDCM <3	3000 K	111 lm/W	2100 lm
93084600	DN570B LED24S/830 PSU-E F WH	(0.43, 0.40) SDCM <3	3000 K	113 lm/W	2600 lm
93085300	DN570B LED24S/840 PSU-E F WH	(0.38, 0.37) SDCM <3	4000 K	124 lm/W	2600 lm
93086000	DN570B LED24S/830 PSD-VLC-E F WH	(0.43, 0.40) SDCM <3	3000 K	113 lm/W	2600 lm
93087700	DN570B LED24S/840 PSD-VLC-E F WH	(0.38, 0.37) SDCM <3	4000 K	124 lm/W	2600 lm
94124800	DN570B LED40S/830 PSU-E F WH	(0.43, 0.40) SDCM <3	3000 K	124 lm/W	4200 lm
94125500	DN570B LED40S/840 PSU-E F WH	(0.38, 0.37) SDCM <3	4000 K	131 lm/W	4200 lm
94127900	DN570B LED40S/840 PSD-VLC-E F WH	(0.38, 0.37) SDCM <3	4000 K	131 lm/W	4200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
93048800	DN570B LED12S/830 PSU-E M WH	(0.43, 0.40) SDCM <3	3000 K	105 lm/W	1150 lm
93049500	DN570B LED12S/830 PSED-VLC-E M WH	(0.43, 0.40) SDCM <3	3000 K	105 lm/W	1150 lm
93060000	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	1850 lm
93061700	DN570B LED20S/830 PSD-VLC-E M WH	(0.43, 0.40) SDCM <3	3000 K	97 lm/W	1850 lm
93050100	DN570B LED12S/830 PSE-E WR WH	(0.43, 0.40) SDCM <3	3000 K	118 lm/W	1300 lm
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	(0.43, 0.40) SDCM <3	3000 K	118 lm/W	1300 lm
93062400	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40) SDCM <3	3000 K	111 lm/W	2100 lm
93105800	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	118 lm/W	1300 lm
93106500	DN571B LED12S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	118 lm/W	1300 lm
93107200	DN571B LED12S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	118 lm/W	1300 lm
93117100	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM <3	3000 K	111 lm/W	2100 lm
93118800	DN571B LED20S/840 PSU-E C WH	(0.38, 0.37) SDCM <3	4000 K	121 lm/W	2100 lm
93119500	DN571B LED20S/830 PSD-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	111 lm/W	2100 lm
93120100	DN571B LED20S/840 PSD-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	121 lm/W	2100 lm
93141600	DN571B LED20S/830	(0.43, 0.40) SDCM <3	3000 K	105 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU-E C PG WH				
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	(0.43, 0.40) SDCM <3	3000 K	105 lm/W	2000 lm
93145400	DN571B LED24S/830 PSE-E C WH	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	2500 lm
93146100	DN571B LED24S/840 PSE-E C WH	(0.38, 0.37) SDCM <3	4000 K	119 lm/W	2500 lm
93147800	DN571B LED24S/830 PSED-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	109 lm/W	2500 lm
93148500	DN571B LED24S/840 PSED-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	119 lm/W	2500 lm
94128600	DN571B LED40S/830 PSE-E C WH	(0.43, 0.40) SDCM <3	3000 K	121 lm/W	4100 lm
94129300	DN571B LED40S/840 PSE-E C WH	(0.38, 0.37) SDCM <3	4000 K	128 lm/W	4100 lm
94130900	DN571B LED40S/830 PSED-VLC-E C WH	(0.43, 0.40) SDCM <3	3000 K	121 lm/W	4100 lm
94131600	DN571B LED40S/840 PSED-VLC-E C WH	(0.38, 0.37) SDCM <3	4000 K	128 lm/W	4100 lm
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2100 lm
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	(0.43, 0.40) SDCM <3	3000 K	95 lm/W	2100 lm
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.37) SDCM <3	4000 K	121 lm/W	2100 lm
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	(0.38, 0.37) SDCM <3	4000 K	121 lm/W	2100 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
93109600	DN571B LED12S/830 PSE-E F WH	(0.43, 0.40)	3000 K	118 lm/W	1300 lm
93110200	DN571B LED12S/840 PSU-E F WH	(0.38, 0.37)	4000 K	118 lm/W	1300 lm
93112600	DN571B LED12S/840 PSD-VLC-E F WH	(0.38, 0.37)	4000 K	118 lm/W	1300 lm
93121800	DN571B LED20S/830 PSU-E F WH	(0.43, 0.40)	3000 K	111 lm/W	2100 lm
93122500	DN571B LED20S/840 PSU-E F WH	(0.38, 0.37)	4000 K	121 lm/W	2100 lm
93123200	DN571B LED20S/830 PSD-VLC-E F WH	(0.43, 0.40)	3000 K	111 lm/W	2100 lm
93124900	DN571B LED20S/840 PSD-VLC-E F WH	(0.38, 0.37)	4000 K	121 lm/W	2100 lm
93149200	DN571B LED24S/830 PSE-E F WH	(0.43, 0.40)	3000 K	109 lm/W	2500 lm
93150800	DN571B LED24S/840 PSE-E F WH	(0.38, 0.37)	4000 K	119 lm/W	2500 lm
93151500	DN571B LED24S/830	(0.43, 0.40)	3000 K	109 lm/W	2500 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSED-VLC-E F WH				
93152200	DN571B LED24S/840 PSED-VLC-E F WH	(0.38, 0.37)	4000 K	119 lm/W	2500 lm
94132300	DN571B LED40S/830 PSE-E F WH	(0.43, 0.40)	3000 K	121 lm/W	4100 lm
94133000	DN571B LED40S/840 PSE-E F WH	(0.38, 0.37)	4000 K	128 lm/W	4100 lm
94134700	DN571B LED40S/830 PSED-VLC-E F WH	(0.43, 0.40)	3000 K	121 lm/W	4100 lm
94135400	DN571B LED40S/840 PSED-VLC-E F WH	(0.38, 0.37)	4000 K	128 lm/W	4100 lm
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	(0.43, 0.40)	3000 K	114 lm/W	1250 lm
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	(0.43, 0.40)	3000 K	105 lm/W	2000 lm
93126300	DN571B LED20S/830 PSD-VLC-E M WH	(0.43, 0.40)	3000 K	87 lm/W	1650 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
93042600	DN570B LED12S/830 PSD-VLC-E C WH	11 W
93043300	DN570B LED12S/840 PSD-VLC-E C WH	11 W
93052500	DN570B LED20S/830 PSU-E C WH	19 W
93053200	DN570B LED20S/840 PSU-E C WH	17.4 W
93054900	DN570B LED20S/830 PSD-VLC-E C WH	19 W
93076100	DN570B LED20S/830 PSU-E C PG WH	19 W
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	19 W
93080800	DN570B LED24S/830 PSU-E C WH	23 W
93081500	DN570B LED24S/840 PSU-E C WH	21 W
93082200	DN570B LED24S/830 PSD-VLC-E C WH	23 W
93083900	DN570B LED24S/840 PSD-VLC-E C WH	21 W
93102700	DN570B LED20S/830 PSU-E C WH SG-O	19 W
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	19 W
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	19 W

Order Code	Full Product Name	Initial input power
94120000	DN570B LED40S/830 PSU-E C WH	34 W
94121700	DN570B LED40S/840 PSU-E C WH	32 W
94122400	DN570B LED40S/830 PSD-VLC-E C WH	34 W
94123100	DN570B LED40S/840 PSD-VLC-E C WH	32 W
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	22 W
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	17.4 W
93044000	DN570B LED12S/830 PSU-E F WH	11 W
93045700	DN570B LED12S/840 PSU-E F WH	11 W
93046400	DN570B LED12S/830 PSED-VLC-E F WH	11 W
93047100	DN570B LED12S/840 PSD-VLC-E F WH	11 W
93056300	DN570B LED20S/830 PSU-E F WH	19 W
93057000	DN570B LED20S/840 PSU-E F WH	17.4 W
93058700	DN570B LED20S/830 PSD-VLC-E F WH	19 W
93059400	DN570B LED20S/840 PSD-VLC-E F WH	17.4 W

## LuxSpace, recessed

Order Code	Full Product Name	Initial input power
93078500	DN570B LED20S/830 PSU-E F PG WH	19 W
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	19 W
93084600	DN570B LED24S/830 PSU-E F WH	23 W
93085300	DN570B LED24S/840 PSU-E F WH	21 W
93086000	DN570B LED24S/830 PSD-VLC-E F WH	23 W
93087700	DN570B LED24S/840 PSD-VLC-E F WH	21 W
94124800	DN570B LED40S/830 PSU-E F WH	34 W
94125500	DN570B LED40S/840 PSU-E F WH	32 W
94127900	DN570B LED40S/840 PSD-VLC-E F WH	32 W
93048800	DN570B LED12S/830 PSU-E M WH	11 W
93049500	DN570B LED12S/830 PSED-VLC-E M WH	11 W
93060000	DN570B LED20S/830 PSU-E M WH	19 W
93061700	DN570B LED20S/830 PSD-VLC-E M WH	19 W
93050100	DN570B LED12S/830 PSE-E WR WH	11 W
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	11 W
93062400	DN570B LED20S/830 PSU-E WR WH	19 W
93105800	DN571B LED12S/830 PSU-E C WH	11 W
93106500	DN571B LED12S/840 PSU-E C WH	11 W
93107200	DN571B LED12S/830 PSD-VLC-E C WH	11 W
93117100	DN571B LED20S/830 PSU-E C WH	19 W
93118800	DN571B LED20S/840 PSU-E C WH	17.4 W
93119500	DN571B LED20S/830 PSD-VLC-E C WH	19 W
93120100	DN571B LED20S/840 PSD-VLC-E C WH	17.4 W
93141600	DN571B LED20S/830 PSU-E C PG WH	19 W
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	19 W
93145400	DN571B LED24S/830 PSE-E C WH	23 W
93146100	DN571B LED24S/840 PSE-E C WH	21 W
93147800	DN571B LED24S/830 PSED-VLC-E C WH	23 W

Order Code	Full Product Name	Initial input power
93148500	DN571B LED24S/840 PSED-VLC-E C WH	21 W
94128600	DN571B LED40S/830 PSE-E C WH	34 W
94129300	DN571B LED40S/840 PSE-E C WH	32 W
94130900	DN571B LED40S/830 PSED-VLC-E C WH	34 W
94131600	DN571B LED40S/840 PSED-VLC-E C WH	32 W
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	22 W
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	22 W
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	17.4 W
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	17.4 W
93109600	DN571B LED12S/830 PSE-E F WH	11 W
93110200	DN571B LED12S/840 PSU-E F WH	11 W
93112600	DN571B LED12S/840 PSD-VLC-E F WH	11 W
93121800	DN571B LED20S/830 PSU-E F WH	19 W
93122500	DN571B LED20S/840 PSU-E F WH	17.4 W
93123200	DN571B LED20S/830 PSD-VLC-E F WH	19 W
93124900	DN571B LED20S/840 PSD-VLC-E F WH	17.4 W
93149200	DN571B LED24S/830 PSE-E F WH	23 W
93150800	DN571B LED24S/840 PSE-E F WH	21 W
93151500	DN571B LED24S/830 PSED-VLC-E F WH	23 W
93152200	DN571B LED24S/840 PSED-VLC-E F WH	21 W
94132300	DN571B LED40S/830 PSE-E F WH	34 W
94133000	DN571B LED40S/840 PSE-E F WH	32 W
94134700	DN571B LED40S/830 PSED-VLC-E F WH	34 W
94135400	DN571B LED40S/840 PSED-VLC-E F WH	32 W
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	11 W
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	19 W
93126300	DN571B LED20S/830 PSD-VLC-E M WH	19 W

### Light Technical

Order Code	Full Product Name	Optical cover/lens acc. type
93042600	DN570B LED12S/830 PSD-VLC-E C WH	No
93043300	DN570B LED12S/840 PSD-VLC-E C WH	No
93052500	DN570B LED20S/830 PSU-E C WH	No
93053200	DN570B LED20S/840 PSU-E C WH	No
93054900	DN570B LED20S/830 PSD-VLC-E C WH	No
93076100	DN570B LED20S/830 PSU-E C PG WH	PG
93077800	DN570B LED20S/830 PSD-VLC-E C PG WH	PG
93080800	DN570B LED24S/830 PSU-E C WH	No
93081500	DN570B LED24S/840 PSU-E C WH	No
93082200	DN570B LED24S/830 PSD-VLC-E C WH	No
93083900	DN570B LED24S/840 PSD-VLC-E C WH	No
93102700	DN570B LED20S/830 PSU-E C WH SG-O	No
93103400	DN570B LED20S/830 PSU-E C WH SG-FRC	No
93104100	DN570B LED20S/830 PSU-E C WH SG-HR-FR	No
94120000	DN570B LED40S/830 PSU-E C WH	No
94121700	DN570B LED40S/840 PSU-E C WH	No
94122400	DN570B LED40S/830 PSD-VLC-E C WH	No
94123100	DN570B LED40S/840 PSD-VLC-E C WH	No
94377800	DN570B LED20S/830 PSU-E C ELP3 WH	-


Order Code	Full Product Name	Optical cover/lens acc. type
94379200	DN570B LED20S/840 PSU-E C ELP3 WH	-
93044000	DN570B LED12S/830 PSU-E F WH	No
93045700	DN570B LED12S/840 PSU-E F WH	No
93046400	DN570B LED12S/830 PSED-VLC-E F WH	No
93047100	DN570B LED12S/840 PSD-VLC-E F WH	No
93056300	DN570B LED20S/830 PSU-E F WH	No
93057000	DN570B LED20S/840 PSU-E F WH	No
93058700	DN570B LED20S/830 PSD-VLC-E F WH	No
93059400	DN570B LED20S/840 PSD-VLC-E F WH	No
93078500	DN570B LED20S/830 PSU-E F PG WH	PG
93079200	DN570B LED20S/830 PSD-VLC-E F PG WH	PG
93084600	DN570B LED24S/830 PSU-E F WH	No
93085300	DN570B LED24S/840 PSU-E F WH	No
93086000	DN570B LED24S/830 PSD-VLC-E F WH	No
93087700	DN570B LED24S/840 PSD-VLC-E F WH	No
94124800	DN570B LED40S/830 PSU-E F WH	No
94125500	DN570B LED40S/840 PSU-E F WH	No
94127900	DN570B LED40S/840 PSD-VLC-E F WH	No
93048800	DN570B LED12S/830 PSU-E M WH	No

## LuxSpace, recessed


Order Code	Full Product Name	Optical cover/lens acc. type
93049500	DN570B LED12S/830 PSED-VLC-E M WH	No
93060000	DN570B LED20S/830 PSU-E M WH	No
93061700	DN570B LED20S/830 PSD-VLC-E M WH	No
93050100	DN570B LED12S/830 PSE-E WR WH	No
93051800	DN570B LED12S/830 PSD-VLC-E WR WH	No
93062400	DN570B LED20S/830 PSU-E WR WH	No
93105800	DN571B LED12S/830 PSU-E C WH	No
93106500	DN571B LED12S/840 PSU-E C WH	No
93107200	DN571B LED12S/830 PSD-VLC-E C WH	No
93117100	DN571B LED20S/830 PSU-E C WH	No
93118800	DN571B LED20S/840 PSU-E C WH	No
93119500	DN571B LED20S/830 PSD-VLC-E C WH	No
93120100	DN571B LED20S/840 PSD-VLC-E C WH	No
93141600	DN571B LED20S/830 PSU-E C PG WH	PG
93142300	DN571B LED20S/830 PSD-VLC-E C PG WH	PG
93145400	DN571B LED24S/830 PSE-E C WH	No
93146100	DN571B LED24S/840 PSE-E C WH	No
93147800	DN571B LED24S/830 PSED-VLC-E C WH	No
93148500	DN571B LED24S/840 PSED-VLC-E C WH	No
94128600	DN571B LED40S/830 PSE-E C WH	No
94129300	DN571B LED40S/840 PSE-E C WH	No
94130900	DN571B LED40S/830 PSED-VLC-E C WH	No
94131600	DN571B LED40S/840 PSED-VLC-E C WH	No

Order Code	Full Product Name	Optical cover/lens acc. type
94381500	DN571B LED20S/830 PSU-E C ELP3 WH	-
94383900	DN571B LED20S/830 PSD-VLC-E C ELP3 WH	-
94382200	DN571B LED20S/840 PSU-E C ELP3 WH	-
94384600	DN571B LED20S/840 PSD-VLC-E C ELP3 WH	-
93109600	DN571B LED12S/830 PSE-E F WH	No
93110200	DN571B LED12S/840 PSU-E F WH	No
93112600	DN571B LED12S/840 PSD-VLC-E F WH	No
93121800	DN571B LED20S/830 PSU-E F WH	No
93122500	DN571B LED20S/840 PSU-E F WH	No
93123200	DN571B LED20S/830 PSD-VLC-E F WH	No
93124900	DN571B LED20S/840 PSD-VLC-E F WH	No
93149200	DN571B LED24S/830 PSE-E F WH	No
93150800	DN571B LED24S/840 PSE-E F WH	No
93151500	DN571B LED24S/830 PSED-VLC-E F WH	No
93152200	DN571B LED24S/840 PSED-VLC-E F WH	No
94132300	DN571B LED40S/830 PSE-E F WH	No
94133000	DN571B LED40S/840 PSE-E F WH	No
94134700	DN571B LED40S/830 PSED-VLC-E F WH	No
94135400	DN571B LED40S/840 PSED-VLC-E F WH	No
93116400	DN571B LED12S/830 PSD-VLC-E WR WH	No
93128700	DN571B LED20S/830 PSD-VLC-E WR WH	No
93126300	DN571B LED20S/830 PSD-VLC-E M WH	No


### Polar Wide Diagrams



IFPS\_DN570B 1xLED12S/840 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/840 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/830 PSE-E C-Polar  
Normal (separate)




Polar Wide Diagrams




IFPS\_DN570B 1xLED12S/827 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/930 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/930 PSE-E C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/830 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/930 C-Polar  
Normal (separate)



IFPS\_DN570B 1xLED12S/830 PSED-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSED-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/840 PSED-E C-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED24S/840 PSED-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/827 PSED-E C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/827 PSED-E C-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/827 C-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/830 C-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/840 C-Polar  
Normal (separate)



IFPS\_DN570B PSED-E 1xLED20S/827 C-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED20S/840 C-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSE-E F-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED20S/830 PSE-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/840 PSE-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/827 PSE-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E F-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/827 F-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/830 F-Polar  
Normal (separate)



IFPS\_DN570B PSE-E 1xLED12S/840 F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSED-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/830 PSED-E F-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED12S/930 PSED-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/827 PSED-E F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSED-E F-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/827 F-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/830 F-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/840 F-Polar  
Normal (separate)



IFPS\_DN570B PSED-E 1xLED12S/930 F-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSE-E M-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED20S/840 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/830 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/840 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/827 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/827 PSE-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E M-Polar  
Normal (separate)



IFPS\_DN570B PSE-E 1xLED12S/827 M-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/830 M-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/840 M-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED12S/830 PSED-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSED-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/930 PSED-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/827 PSED-E M-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/827 PSED-E M-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/840 M-Polar  
Normal (separate)



IFPS\_DN570B 1xLED12S/830 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSE-E WR-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED24S/830 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/840 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/827 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED24S/827 PSE-E WR-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED12S/827 WR-Polar  
Normal (separate)



IFPS\_DN570B PSE-E 1xLED12S/830 WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED12S/840 PSED-E WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSED-E WR-  
Polar Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED20S/840 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B 1xLED24S/830 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B 1xLED24S/840 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B 1xLED12S/827 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B 1xLED24S/827 PSED-E WR-Polar Normal (separate)



IFPS\_DN570B 1xLED24S/930 PSED-E WR-Polar Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/827 WR-Polar Normal (separate)




IFPS\_DN570B PSED-E 1xLED12S/840 WR-Polar Normal (separate)




Polar Wide Diagrams




IFPS\_DN570B PSE-E 1xLED20S/830 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/930 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED24S/827 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED24S/840 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED24S/930 C-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/827 F-Polar  
Normal (separate)



IFPS\_DN570B PSE-E 1xLED20S/840 F-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED20S/830 F-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/830 M-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B PSE-E 1xLED20S/930 M-Polar  
Normal (separate)




IFPS\_DN570B PSED-E 1xLED20S/840 M-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/830 WR-Polar  
Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/840 WR-Polar  
Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSE-E C PG-  
Polar Normal (separate)




IFPS\_DN570B 1xLED20S/840 PSE-E C PG-  
Polar Normal (separate)



IFPS\_DN570B 1xLED20S/827 PSED-E C PG-  
Polar Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSED-E C PG-  
Polar Normal (separate)




IFPS\_DN570B 1xLED12S/830 PSE-E F PG-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B 1xLED12S/840 PSE-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSE-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED24S/840 PSE-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED12S/830 PSED-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/840 PSED-E F PG-Polar Normal (separate)



IFPS\_DN570B 1xLED24S/830 PSED-E F PG-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSED-E F PG-Polar Normal (separate)




IFPS\_DN570B PSE-E 1xLED24S/830 F-Polar Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B PSE-E 1xLED24S/930 F-Polar Normal (separate)




IFPS\_DN570B PSED-E 1xLED24S/830 F-Polar Normal (separate)




IFPS\_DN570B PSED-E 1xLED24S/930 F-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/830 PSE-E C SG-O-Polar Normal (separate)




IFPS\_DN570B 1xLED20S/930 PSE-E C SG-O-Polar Normal (separate)




IFPS\_DN570B 1xLED12S/830 PSE-E C SG-FRC-Polar Normal (separate)



IFPS\_DN570B 1xLED20S/840 PSE-E C SG-FRC-Polar Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/827 C SG-FRC-Polar Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/830 C SG-FRC-Polar Normal (separate)


Polar Wide Diagrams




IFPS\_DN570B PSE-E 1xLED20S/840 C SG-FRC-Polar Normal (separate)




IFPS\_DN570B PSE-E 1xLED20S/930 C SG-FRC-Polar Normal (separate)




IFPS\_DN571B 1xLED12S/840 PSE-E C-Polar Normal (separate)




IFPS\_DN571B 1xLED20S/830 PSE-E C-Polar Normal (separate)




IFPS\_DN571B 1xLED24S/827 PSE-E C-Polar Normal (separate)




IFPS\_DN571B PSE-E 1xLED12S/840 C-Polar Normal (separate)



IFPS\_DN571B 1xLED12S/830 PSED-E C-Polar Normal (separate)




IFPS\_DN571B 1xLED20S/830 PSED-E C-Polar Normal (separate)




IFPS\_DN571B 1xLED20S/840 PSED-E C-Polar Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B 1xLED24S/830 PSED-E C-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSED-E C-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/827 PSED-E C-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/930 PSED-E C-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/930 PSED-E C-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/930 PSED-E C-Polar  
Normal (separate)



IFPS\_DN571B PSED-E 1xLED12S/827 C-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED12S/830 C-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED12S/930 C-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B 1xLED12S/830 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/830 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/830 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/827 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/827 PSE-E F-Polar  
Normal (separate)



IFPS\_DN571B 1xLED24S/930 PSE-E F-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED12S/830 F-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED12S/930 F-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B 1xLED12S/830 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/840 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/830 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/827 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED12S/830 F-Polar  
Normal (separate)



IFPS\_DN571B PSED-E 1xLED12S/930 F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/827 PSED-E F-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/830 PSED-E M-Polar  
Normal (separate)




Polar Wide Diagrams




IFPS\_DN571B 1xLED20S/840 PSED-E M-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSED-E M-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/930 PSED-E M-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/827 PSED-E M-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/840 PSED-E WR-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/830 PSED-E WR-Polar  
Normal (separate)



IFPS\_DN571B 1xLED20S/840 PSED-E WR-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSED-E WR-Polar  
Normal (separate)




IFPS\_DN571B 1xLED12S/827 PSED-E WR-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B PSED-E 1xLED12S/840 WR-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED20S/827 C-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED20S/930 C-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED24S/827 C-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED24S/840 C-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED24S/930 C-Polar  
Normal (separate)



IFPS\_DN571B PSED-E 1xLED20S/840 C-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/930 C-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED20S/830 F-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B PSE-E 1xLED20S/930 F-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/840 F-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/930 F-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/840 M-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/930 M-Polar  
Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/827 WR-Polar  
Normal (separate)



IFPS\_DN571B 1xLED20S/830 PSE-E C PG-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/830 PSE-E C PG-Polar  
Normal (separate)




IFPS\_DN571B 1xLED24S/840 PSE-E C PG-Polar  
Normal (separate)


Polar Wide Diagrams




IFPS\_DN571B PSE-E 1xLED20S/827 C PG-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED20S/830 C PG-Polar  
Normal (separate)




IFPS\_DN571B PSE-E 1xLED20S/930 C PG-Polar  
Normal (separate)




IFPS\_DN571B 1xLED20S/827 PSED-E C PG-  
Polar Normal (separate)




IFPS\_DN571B PSED-E 1xLED20S/930 C PG-  
Polar Normal (separate)




IFPS\_DN571B PSED-E 1xLED24S/930 C-Polar  
Normal (separate)



IFPS\_DN571B PSE-E 1xLED24S/827 F-Polar  
Normal (separate)



IFPS\_DN571B PSE-E 1xLED24S/830 F-Polar  
Normal (separate)



IFPS\_DN571B PSED-E 1xLED24S/930 F-Polar  
Normal (separate)

