



# Standard electromagnetic ballast for compact fluorescent applications

## BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.

### Benefits

- Reliable electrical and mechanical performance
- Reliable electrical and mechanical performance
- Optimum lamp performance under optimum temperature conditions
- Optimum lamp performance under optimum temperature conditions
- Fits compact luminaires
- Fits compact luminaires

### Features

- Long lifetime
- Long lifetime
- Compact design
- Compact design
- Quick and easy wiring
- Quick and easy wiring
- High-quality screw-in or insert contact
- High-quality screw-in or insert contact

## BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

### Application

- Retail
- Retail
- Offices
- Offices
- Industry
- Industry
- Home
- Home

