



# Standard electromagnetic ballast for fluorescent applications

## BTA EM ballasts for TL Fluorescent lamps

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.

### Benefits

- Reliable electrical and mechanical performance
- Compact dimensions
- Electrical design for optimum lamp performance

### Features

- Long lifetime
- Quick and easy wiring
- Easy to recognize: blue product label
- Tw marking 130 °C (means average lifetime of 10 years' continuous operation @ 130 °C)
- High-quality screw-in or insert contact

### Application

- Retail
- Offices
- Industry
- Home