

Value-for-money electromagnetic ballast for fluorescent applications

BT-ALU EM ballasts for TL Fluorescent lamps

Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps; ideal solution for economical high-quality performance

Benefits

- Reliable electrical and mechanical performance
- Guaranteed quality level, light output >80%
- Noise reduction, thanks to embossed mounting plate

Features

- Long lifetime
- Quick and easy wiring
- Easy to recognize: blue product label
- Tw marking 130 °C (means average lifetime of 10 years' continuous operation @ 130 °C)
- High-quality screw-in or insert contact

Application

- Signage
- Parking areas/outdoor
- Industry (low bay)


BT-ALU EM ballasts for TL Fluorescent lamps

Versions



BT-ALU 18W 220V C SC

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BT-ALU 18W	4.0	28.0	1.2	155.0	140.0	48.0	72.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

