



Digital ignitors for maximum reliability

Electronic digital control ignitor for HID lamp circuits

HID ignitors for series systems

Benefits

- Easy installation and wiring
- Can operate with both semi-parallel and series ballasts
- Digital ignitors ensure maximum reliability

Features

- Ignitors equipped with screw terminal blocks as standard
- Series ignitor will only work in series circuits

Application

- Outdoor lighting (most popular application: road and tunnel lighting)


Versions



SU 42-S

Electronic digital control ignitor for HID lamp circuits

Dimensional drawing



Product	A2	C1	A1	B1
SU 42-S	63.4 mm	34 mm	96 mm	45 mm

