

BPL EM ballasts for CFL, PLT, PLS and PLC lamps

BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

Range of copper ballasts produced with a high level of accuracy on current settings to ensure optimum operation of compact fluorescent lamps. Designed for compact fluorescent lamps to be operated on 240 V-50 Hz mains supply.

Benefits

- Optimum lamp performance under optimum temperature conditions

Features

- Low watt loss
- Long life
- Quick and easy wiring
- Compact
- Minimal rise in temperature

Application

- Retail
- Office buildings and industry
- Homes


BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

Versions



BPL 018 X262

Dimensional drawing



Product	D1	C1	A1	A2	B1
BPL 018 X261	4.2 mm	28.0 mm	87.0 mm	70.0 mm	39.0 mm

