



# Gamme d'accessoires :

## OccuSwitch Classic

Notre gamme d'accessoires se compose d'interfaces utilisateur, de capteurs, de câbles et bien d'autres, tous compatibles avec la totalité de nos systèmes ainsi que ceux de certains autres fabricants. La gamme inclut également un potentiomètre pouvant être utilisés de manière autonome (pour des ballasts 1-10 V) ou avec notre système Trios. La performance et la capacité des produits varient en fonction du système de gestion auquel ils sont connectés.

### Avantages

- Les accessoires d'intérieur offrent la possibilité d'étendre les systèmes de commande de l'éclairage d'intérieur.

### Fonctions

- Les performances et les capacités des produits peuvent varier en fonction du système auquel ils sont connectés.

### Application

- Tertiaire

### Versions

UID8470 Switch



LCN3120 OCC Sensor IP65



# OccuSwitch Classic

## Versions

OCC 0101A02 DL BP Sensor WH  
product photo



LCN1840/05 Interact Pro wireless  
gateway product photo



LCN3110 OCC Sensor IP65



IRT9015/00 Interact Retrofit  
Commissioning Remote Control



Interact Ready RF-DALI Connector  
Kit



UID8480 Switch





OCC 0100A02 BP Sensor WH  
product photo



# OccuSwitch Classic

## Schéma dimensionnel



## Détails sur le produit

UID8470 Switch Detail Photo Back



UID8480 Switch Detail Photo Front



UID8470 Switch Detail Photo Front



UID8480 Switch Detail Photo Back

