



MBR902 – The best value

MBR/MBS902

The MBR/S 902 range has been designed for use in sheltered outdoor areas such as gas stations. Totally protected against dust and insects, it is an excellent choice at a very attractive price.

Benefits

- Lightweight, compact
- Philips solution: lamp, ballast, and luminaire
- Stainless steel screws provide greater corrosion resistance
- High-gloss anodized aluminum reflector ensures excellent light distribution
- Tempered glass front
- Available in symmetrical and asymmetrical versions

Features

- Easy installation and interior access for maintenance
- Surface-mounted (MBR) or recessed (MBS)
- Gaskets to prevent the accumulation of dirt and to stop insects from entering
- Anti-glare wings provide excellent visual comfort

Application

- Gas stations
- Sheltered outdoor areas


Specifications

Type	MBR902
	MBS902
Power supply	220 V

Frequency	60 Hz
Power and lamp models	1 x HPI-T / E40 / 250, 400 W

MBR/MBS902


Versions



Accessories



Ordercode 919506015071



Ordercode 919506015101

General Information

Lamp family code HPI-TP

General Information

Order Code	Full Product Name	Lamp power	Optic type
919306015061	MBR902 HPI-T250W K A	250 W	Asymmetrical
919306015081	MBR902 HPI-T400W K A	400 W	Asymmetrical

Order Code	Full Product Name	Lamp power	Optic type
919306015071	MBS902 HPI-T250W K S	250 W	Symmetrical
919306015091	MBS902 HPI-T400W K S	400 W	Symmetrical

