



# A flexible and affordable retail toolbox

## GreenSpace Accent Elbow

Thanks to the GreenSpace Accent family, retailers and building operators can make the switch from CDM to LED and enjoy Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Elbow's regular cut-out makes retrofit installation quick and easy by a single installer. For food retailers, GreenSpace Accent Elbow comes with special light recipes to enhance the store ambiance and show the produce in the very best light: Fresh Food Champagne is the perfect solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance, while Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance. Fashion retailers can also choose from a variety of light flavors: CrispWhite is the clear choice to make colors appear rich and intense while keeping whites bright, and PremiumWhite is the best CDM alternative for high color rendering in a warm lighting ambiance.

### Benefits

- Hassle-free replacement of CDM recessed luminaires
- Short payback compared with CDM luminaires due to high system efficacy
- High-quality accent lighting thanks to PerfectAccent reflector's light signature

### Features

- High efficacy
- Philips PerfectAccent quality of light
- CDM retrofit recessed luminaire; easy to install
- Clean, robust design

# GreenSpace Accent Elbow

## Application

- Retail stores, especially food and fashion stores
- Public spaces such as shopping malls, train stations, airports, etc.

## Specifications

<b>Type</b>	RS342B	<b>Performance Ambient Temperature Tq</b>	+25 °C
<b>Ceiling type</b>	Plaster (board) ceiling	<b>Operating temperature range</b>	0 to +35 °C
<b>Light source</b>	Non-replaceable LED module	<b>Driver</b>	Separate
<b>Power</b>	18, 29 and 38.5 W (for light color 830, LED17S, LED27S, LED39S) 30 and 46.5 W (for light color Fresh Food Meat, LED19S and LED26S) 44 W (for light color Fresh Food Champagne, LED27S) 21, 33 and 50 W (for CrispWhite LED17S, LED27S, LED39S) 19.4, 28.5 and 48.5 W (for PremiumWhite LED17S, LED27S, LED39S)	<b>Mains voltage</b>	220-240 V / 50-60 Hz
<b>Beam angle</b>	12° (NB), 25° (MB), 37° (WB)	<b>Dimming</b>	DALI dimming and Constant Light Output
<b>Luminous flux</b>	1700, 2700, 3900 lm (for light color 830) 1900 or 2600 lm (for light color Fresh Food Meat, LED19S or LED26S) 2600 lm (for light color Fresh Food Champagne, LED27S) 1700, 2700, 3600 lm (for light color CrispWhite)	<b>Material</b>	Housing and rim: die-cast aluminum Cover: acrylic
<b>Correlated Color Temperature</b>	2700, 3000 and 4000 K (827, 830, 840) Fresh Food Meat (FMT) Fresh Food Champagne (CH) CrispWhite (CRW) PremiumWhite (PW9)	<b>Color</b>	White (RAL9003), silver (RAL9006) and black (RAL9004)
<b>Color Rendering Index</b>	>80 (for 2700, 3000 and 4000 K) >90 (for Fresh Food Champagne, Fresh Food Meat and PremiumWhite) >92 (for CrispWhite)	<b>Connection</b>	Push-in connector or with pull relief Wieland/Adels compatible connector with cable length 0.5 m (CW) Push-in connector with loop through wiring enabled for non DALI versions (CU3) Push-in connector with loop through wiring enabled for DALI versions (CU5)
<b>Standard deviation color matching (SDCM)</b>	3 (with a tolerance of +/- 0,005 on color point measurement)	<b>Installation</b>	Fixation by means of spring fasteners
<b>Lumen maintenance at 50000 h median useful life*</b>	L80	<b>Remarks</b>	Fresh Food Champagne (CH) is the dedicated light recipe for bread and pastries, fruits and vegetables area. It brings a warm traditional ambiance. Fresh Food Meat (FMT) is a dedicated light recipe for meat counters. It brings a natural cool light setting. CrispWhite (CRW) is the dedicated light recipe for fashion retailers which makes whites appear pure and bright while at the same time making other colours appear warm, saturated and intense PremiumWhite is the best CDM Elite alternative for high color rendering with a warm color of light for fashion and food retailers.
<b>Control gear failure rate at median useful life 50000 h</b>	5%		

# GreenSpace Accent Elbow

## Versions



GreenSpace Accent elbow RS342B  
downlight



GreenSpace Accent elbow RS342B  
downlight



GreenSpace Accent elbow RS342B  
downlight

## Product details



GreenSpace Accent elbow, fully  
recessed



GreenSpace Accent elbow,  
extracted



GreenSpace Accent elbow,  
extracted



GreenSpace Accent elbow, front  
face

# GreenSpace Accent Elbow

## Product details




GreenSpace Accent elbow, back view



GreenSpace Accent elbow, fully recessed



GreenSpace Accent elbow, extracted



GreenSpace Accent elbow, fully recessed



GreenSpace Accent elbow, extracted

## Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

## General Information

Beam angle of light source	120 °
Cap-Base	-
CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
ENEC mark	ENEC mark
Gear	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1 pc
Product Family Code	RS342B
UL mark	-

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500456512	RS342B LED17S/830 PSU-E MB BK	+10 to +40 °C	Not applicable	No
910500456513	RS342B LED17S/840 PSU-E MB BK	+10 to +40 °C	Not applicable	No
910500456514	RS342B LED17S/830 PSU-E WB BK	+10 to +40 °C	Not applicable	No
910500456515	RS342B LED17S/840 PSU-E WB BK	+10 to +40 °C	Not applicable	No
910500456524	RS342B LED27S/830 PSU-E MB BK	+10 to +40 °C	Not applicable	No
910500456525	RS342B LED27S/840 PSU-E MB BK	+10 to +40 °C	Not applicable	No
910500456526	RS342B LED27S/830 PSU-E WB BK	+10 to +40 °C	Not applicable	No
910500456527	RS342B LED27S/840 PSU-E WB BK	+10 to +40 °C	Not applicable	No
910500456516	RS342B LED17S/830 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500456517	RS342B LED17S/840 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500456518	RS342B LED17S/830 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500456519	RS342B LED17S/840 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500456522	RS342B LED17S/830 PSU-E WB SI	+10 to +40 °C	Not applicable	No
910500456523	RS342B LED17S/840 PSU-E WB SI	+10 to +40 °C	Not applicable	No
910500456528	RS342B LED27S/830 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500456529	RS342B LED27S/840 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500456530	RS342B LED27S/830 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500456531	RS342B LED27S/840 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500457072	RS342B LED19S/FMT PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500458816	RS342B LED27S/827 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500458817	RS342B LED27S/PW930 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500458819	RS342B LED39S/PW930 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500458884	RS342B LED17S/PW930 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500458885	RS342B LED27S/FMT PSU-E MB WH	+10 to +40 °C	Not applicable	No

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500458889	RS342B LED39S/830 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500458890	RS342B LED39S/840 PSU-E MB WH	+10 to +40 °C	Not applicable	No
910500459011	RS342B LED17S/PW930 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459012	RS342B LED27S/PW930 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459013	RS342B LED39S/827 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459014	RS342B LED39S/830 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459015	RS342B LED39S/840 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459016	RS342B LED39S/PW930 PSU-E WB WH	+10 to +40 °C	Not applicable	No
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	+10 to +40 °C	Not applicable	No
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	+10 to +40 °C	1%	No
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	+10 to +40 °C	Not applicable	No
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	+10 to +40 °C	1%	No
910500465707	RS342B LED27S/PC930 PSU-E MB WH	+10 to +25 °C	-	Yes
910500465708	RS342B LED39S/PC930 PSU-E MB WH	+10 to +25 °C	-	Yes
910500456520	RS342B LED17S/830 PSU-E MB SI	+10 to +40 °C	Not applicable	No
910500456521	RS342B LED17S/840 PSU-E MB SI	+10 to +40 °C	Not applicable	No
910500456532	RS342B LED27S/830 PSU-E MB SI	+10 to +40 °C	Not applicable	No
910500456533	RS342B LED27S/840 PSU-E MB SI	+10 to +40 °C	Not applicable	No
910500456534	RS342B LED27S/830 PSU-E WB SI	+10 to +40 °C	Not applicable	No
910500456535	RS342B LED27S/840 PSU-E WB SI	+10 to +40 °C	Not applicable	No

**Controls and Dimming**

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910500456512	RS342B LED17S/830 PSU-E MB BK	No	910500456526	RS342B LED27S/830 PSU-E WB BK	No
910500456513	RS342B LED17S/840 PSU-E MB BK	No	910500456527	RS342B LED27S/840 PSU-E WB BK	No
910500456514	RS342B LED17S/830 PSU-E WB BK	No	910500456516	RS342B LED17S/830 PSU-E MB WH	No
910500456515	RS342B LED17S/840 PSU-E WB BK	No	910500456517	RS342B LED17S/840 PSU-E MB WH	No
910500456524	RS342B LED27S/830 PSU-E MB BK	No	910500456518	RS342B LED17S/830 PSU-E WB WH	No
910500456525	RS342B LED27S/840 PSU-E MB BK	No	910500456519	RS342B LED17S/840 PSU-E WB WH	No

## GreenSpace Accent Elbow

Order Code	Full Product Name	Dimmable
910500456522	RS342B LED17S/830 PSU-E WB SI	No
910500456523	RS342B LED17S/840 PSU-E WB SI	No
910500456528	RS342B LED27S/830 PSU-E MB WH	No
910500456529	RS342B LED27S/840 PSU-E MB WH	No
910500456530	RS342B LED27S/830 PSU-E WB WH	No
910500456531	RS342B LED27S/840 PSU-E WB WH	No
910500457072	RS342B LED19S/FMT PSU-E WB WH	No
910500458816	RS342B LED27S/827 PSU-E MB WH	No
910500458817	RS342B LED27S/PW930 PSU-E MB WH	No
910500458819	RS342B LED39S/PW930 PSU-E MB WH	No
910500458884	RS342B LED17S/PW930 PSU-E MB WH	No
910500458885	RS342B LED27S/FMT PSU-E MB WH	No
910500458889	RS342B LED39S/830 PSU-E MB WH	No
910500458890	RS342B LED39S/840 PSU-E MB WH	No
910500459011	RS342B LED17S/PW930 PSU-E WB WH	No
910500459012	RS342B LED27S/PW930 PSU-E WB WH	No

Order Code	Full Product Name	Dimmable
910500459013	RS342B LED39S/827 PSU-E WB WH	No
910500459014	RS342B LED39S/830 PSU-E WB WH	No
910500459015	RS342B LED39S/840 PSU-E WB WH	No
910500459016	RS342B LED39S/PW930 PSU-E WB WH	No
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	No
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	Yes
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	No
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	Yes
910500465707	RS342B LED27S/PC930 PSU-E MB WH	No
910500465708	RS342B LED39S/PC930 PSU-E MB WH	No
910500456520	RS342B LED17S/830 PSU-E MB SI	No
910500456521	RS342B LED17S/840 PSU-E MB SI	No
910500456532	RS342B LED27S/830 PSU-E MB SI	No
910500456533	RS342B LED27S/840 PSU-E MB SI	No
910500456534	RS342B LED27S/830 PSU-E WB SI	No
910500456535	RS342B LED27S/840 PSU-E WB SI	No

### Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500456512	RS342B LED17S/830 PSU-E MB BK	220-240 V
910500456513	RS342B LED17S/840 PSU-E MB BK	220-240 V
910500456514	RS342B LED17S/830 PSU-E WB BK	220-240 V
910500456515	RS342B LED17S/840 PSU-E WB BK	220-240 V
910500456524	RS342B LED27S/830 PSU-E MB BK	220-240 V
910500456525	RS342B LED27S/840 PSU-E MB BK	220-240 V
910500456526	RS342B LED27S/830 PSU-E WB BK	220-240 V
910500456527	RS342B LED27S/840 PSU-E WB BK	220-240 V
910500456516	RS342B LED17S/830 PSU-E MB WH	220-240 V
910500456517	RS342B LED17S/840 PSU-E MB WH	220-240 V
910500456518	RS342B LED17S/830 PSU-E WB WH	220-240 V
910500456519	RS342B LED17S/840 PSU-E WB WH	220-240 V
910500456522	RS342B LED17S/830 PSU-E WB SI	220-240 V
910500456523	RS342B LED17S/840 PSU-E WB SI	220-240 V
910500456528	RS342B LED27S/830 PSU-E MB WH	220-240 V
910500456529	RS342B LED27S/840 PSU-E MB WH	220-240 V
910500456530	RS342B LED27S/830 PSU-E WB WH	220-240 V
910500456531	RS342B LED27S/840 PSU-E WB WH	220-240 V
910500457072	RS342B LED19S/FMT PSU-E WB WH	220-240 V
910500458816	RS342B LED27S/827 PSU-E MB WH	220-240 V
910500458817	RS342B LED27S/PW930 PSU-E MB WH	220-240 V
910500458819	RS342B LED39S/PW930 PSU-E MB WH	220-240 V

Order Code	Full Product Name	Input Voltage
910500458884	RS342B LED17S/PW930 PSU-E MB WH	220-240 V
910500458885	RS342B LED27S/FMT PSU-E MB WH	220-240 V
910500458889	RS342B LED39S/830 PSU-E MB WH	220-240 V
910500458890	RS342B LED39S/840 PSU-E MB WH	220-240 V
910500459011	RS342B LED17S/PW930 PSU-E WB WH	220-240 V
910500459012	RS342B LED27S/PW930 PSU-E WB WH	220-240 V
910500459013	RS342B LED39S/827 PSU-E WB WH	220-240 V
910500459014	RS342B LED39S/830 PSU-E WB WH	220-240 V
910500459015	RS342B LED39S/840 PSU-E WB WH	220-240 V
910500459016	RS342B LED39S/PW930 PSU-E WB WH	220-240 V
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	220-240 V
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	220-240 V
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	220-240 V
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	220-240 V
910500465707	RS342B LED27S/PC930 PSU-E MB WH	220 to 240 V
910500465708	RS342B LED39S/PC930 PSU-E MB WH	220 to 240 V
910500456520	RS342B LED17S/830 PSU-E MB SI	220-240 V
910500456521	RS342B LED17S/840 PSU-E MB SI	220-240 V
910500456532	RS342B LED27S/830 PSU-E MB SI	220-240 V
910500456533	RS342B LED27S/840 PSU-E MB SI	220-240 V
910500456534	RS342B LED27S/830 PSU-E WB SI	220-240 V
910500456535	RS342B LED27S/840 PSU-E WB SI	220-240 V

### General Information (1/2)

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare	Lamp
				shielding accessories	family code
910500456512	RS342B LED17S/830	Acrylic bowl/ cover clear	-	-	LED17S

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare	Lamp
				shielding accessories	family code
	PSU-E MB BK				

## GreenSpace Accent Elbow

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare shielding accessories	Lamp family code
910500456513	RS342B LED17S/840 PSU-E MB BK	Acrylic bowl/ cover clear	-	-	LED17S
910500456514	RS342B LED17S/830 PSU-E WB BK	Acrylic bowl/ cover clear	-	-	LED17S
910500456515	RS342B LED17S/840 PSU-E WB BK	Acrylic bowl/ cover clear	-	-	LED17S
910500456524	RS342B LED27S/830 PSU-E MB BK	Acrylic bowl/ cover clear	-	-	LED27S
910500456525	RS342B LED27S/840 PSU-E MB BK	Acrylic bowl/ cover clear	-	-	LED27S
910500456526	RS342B LED27S/830 PSU-E WB BK	Acrylic bowl/ cover clear	-	-	LED27S
910500456527	RS342B LED27S/840 PSU-E WB BK	Acrylic bowl/ cover clear	-	-	LED27S
910500456516	RS342B LED17S/830 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED17S
910500456517	RS342B LED17S/840 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED17S
910500456518	RS342B LED17S/830 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED17S
910500456519	RS342B LED17S/840 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED17S
910500456522	RS342B LED17S/830 PSU-E WB SI	Acrylic bowl/ cover clear	-	-	LED17S
910500456523	RS342B LED17S/840 PSU-E WB SI	Acrylic bowl/ cover clear	-	-	LED17S

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare shielding accessories	Lamp family code
910500456528	RS342B LED27S/830 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500456529	RS342B LED27S/840 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500456530	RS342B LED27S/830 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500456531	RS342B LED27S/840 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500457072	RS342B LED19S/FMT PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED19S
910500458816	RS342B LED27S/827 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500458817	RS342B LED27S/ PW930 PSU- E MB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500458819	RS342B LED39S/ PW930 PSU- E MB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500458884	RS342B LED17S/ PW930 PSU- E MB WH	Acrylic bowl/ cover clear	-	-	LED17S
910500458885	RS342B LED27S/FMT PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED26S
910500458889	RS342B LED39S/830 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500458890	RS342B LED39S/840 PSU-E MB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500459011	RS342B LED17S/ cover clear	Acrylic bowl/ cover clear	-	-	LED17S



## GreenSpace Accent Elbow

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare shielding accessories	Lamp family code
	PW930 PSU- E WB WH				
910500459012	RS342B LED27S/ PW930 PSU- E WB WH	Acrylic bowl/ cover clear	-	-	LED27S
910500459013	RS342B LED39S/827 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500459014	RS342B LED39S/830 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500459015	RS342B LED39S/840 PSU-E WB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500459016	RS342B LED39S/ PW930 PSU- E WB WH	Acrylic bowl/ cover clear	-	-	LED39S
910500459017	RS342B LED27S/ PW930 PSU- E MB WH CW-L	Acrylic bowl/ cover clear	-	-	LED27S
910500459018	RS342B LED27S/ PW930 PSD-VLC-E MB WH CW- L	Acrylic bowl/ cover clear	-	-	LED27S
910500459019	RS342B LED39S/ PW930 PSU- E WB WH CW-L	Acrylic bowl/ cover clear	-	-	LED39S

Order Code	Full Product Name	Optical cover/ lens type	Flammability mark	Glare shielding accessories	Lamp family code
910500459020	RS342B LED39S/ PW930 PSD-VLC-E WB WH CW- L	Acrylic bowl/ cover clear	-	-	LED39S
910500465707	RS342B LED27S/ PC930 PSU- E MB WH	Polycarbonate opal satinized	For mounting on normally flammable surfaces	-	LED27S
910500465708	RS342B LED39S/ PC930 PSU- E MB WH	Polycarbonate opal satinized	For mounting on normally flammable surfaces	-	LED39S
910500456520	RS342B LED17S/830 PSU-E MB SI	Acrylic bowl/ cover clear	-	-	LED17S
910500456521	RS342B LED17S/840 PSU-E MB SI	Acrylic bowl/ cover clear	-	-	LED17S
910500456532	RS342B LED27S/830 PSU-E MB SI	Acrylic bowl/ cover clear	-	-	LED27S
910500456533	RS342B LED27S/840 PSU-E MB SI	Acrylic bowl/ cover clear	-	-	LED27S
910500456534	RS342B LED27S/830 PSU-E WB SI	Acrylic bowl/ cover clear	-	-	LED27S
910500456535	RS342B LED27S/840 PSU-E WB SI	Acrylic bowl/ cover clear	-	-	LED27S

### General Information (2/2)

Order Code	Full Product Name	Optic type
910500456512	RS342B LED17S/830 PSU-E MB BK	Medium beam
910500456513	RS342B LED17S/840 PSU-E MB BK	Medium beam
910500456514	RS342B LED17S/830 PSU-E WB BK	Wide beam
910500456515	RS342B LED17S/840 PSU-E WB BK	Wide beam
910500456524	RS342B LED27S/830 PSU-E MB BK	Medium beam
910500456525	RS342B LED27S/840 PSU-E MB BK	Medium beam
910500456526	RS342B LED27S/830 PSU-E WB BK	Wide beam
910500456527	RS342B LED27S/840 PSU-E WB BK	Wide beam

Order Code	Full Product Name	Optic type
910500456516	RS342B LED17S/830 PSU-E MB WH	Medium beam
910500456517	RS342B LED17S/840 PSU-E MB WH	Medium beam
910500456518	RS342B LED17S/830 PSU-E WB WH	Wide beam
910500456519	RS342B LED17S/840 PSU-E WB WH	Wide beam
910500456522	RS342B LED17S/830 PSU-E WB SI	Wide beam
910500456523	RS342B LED17S/840 PSU-E WB SI	Wide beam
910500456528	RS342B LED27S/830 PSU-E MB WH	Medium beam
910500456529	RS342B LED27S/840 PSU-E MB WH	Medium beam

## GreenSpace Accent Elbow

Order Code	Full Product Name	Optic type
910500456530	RS342B LED27S/830 PSU-E WB WH	Wide beam
910500456531	RS342B LED27S/840 PSU-E WB WH	Wide beam
910500457072	RS342B LED19S/FMT PSU-E WB WH	Wide beam
910500458816	RS342B LED27S/827 PSU-E MB WH	Medium beam
910500458817	RS342B LED27S/PW930 PSU-E MB WH	Medium beam
910500458819	RS342B LED39S/PW930 PSU-E MB WH	Medium beam
910500458884	RS342B LED17S/PW930 PSU-E MB WH	Medium beam
910500458885	RS342B LED27S/FMT PSU-E MB WH	Medium beam
910500458889	RS342B LED39S/830 PSU-E MB WH	Medium beam
910500458890	RS342B LED39S/840 PSU-E MB WH	Medium beam
910500459011	RS342B LED17S/PW930 PSU-E WB WH	Wide beam
910500459012	RS342B LED27S/PW930 PSU-E WB WH	Wide beam
910500459013	RS342B LED39S/827 PSU-E WB WH	Wide beam
910500459014	RS342B LED39S/830 PSU-E WB WH	Wide beam

Order Code	Full Product Name	Optic type
910500459015	RS342B LED39S/840 PSU-E WB WH	Wide beam
910500459016	RS342B LED39S/PW930 PSU-E WB WH	Wide beam
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	Medium beam
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	Medium beam
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	Wide beam
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	Wide beam
910500465707	RS342B LED27S/PC930 PSU-E MB WH	Wide beam
910500465708	RS342B LED39S/PC930 PSU-E MB WH	Wide beam
910500456520	RS342B LED17S/830 PSU-E MB SI	Medium beam
910500456521	RS342B LED17S/840 PSU-E MB SI	Medium beam
910500456532	RS342B LED27S/830 PSU-E MB SI	Medium beam
910500456533	RS342B LED27S/840 PSU-E MB SI	Medium beam
910500456534	RS342B LED27S/830 PSU-E WB SI	Wide beam
910500456535	RS342B LED27S/840 PSU-E WB SI	Wide beam

### Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Init. Color	
			Temperature	Index	Rendering
910500456512	RS342B LED17S/830 PSU-E MB BK	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456513	RS342B LED17S/840 PSU-E MB BK	(0.38, 0.38)	4000 K	≥80	125 lm/W
910500456514	RS342B LED17S/830 PSU-E WB BK	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456515	RS342B LED17S/840 PSU-E WB BK	(0.38, 0.38)	3000 K	≥80	125 lm/W
910500456524	RS342B LED27S/830 PSU-E MB BK	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456525	RS342B LED27S/840 PSU-E MB BK	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Init. Color	
			Temperature	Index	Rendering
910500456526	RS342B LED27S/830 PSU-E WB BK	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456527	RS342B LED27S/840 PSU-E WB BK	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
910500456516	RS342B LED17S/830 PSU-E MB WH	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456517	RS342B LED17S/840 PSU-E MB WH	(0.38, 0.38)	4000 K	≥80	125 lm/W
910500456518	RS342B LED17S/830 PSU-E WB WH	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456519	RS342B LED17S/840 PSU-E WB WH	(0.38, 0.38)	4000 K	≥80	125 lm/W

## GreenSpace Accent Elbow

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
910500456522	RS342B LED17S/830 PSU-E WB SI	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456523	RS342B LED17S/840 PSU-E WB SI	(0.38, 0.38)	4000 K	≥80	125 lm/W
910500456528	RS342B LED27S/830 PSU-E MB WH	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456529	RS342B LED27S/840 PSU-E MB WH	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
910500456530	RS342B LED27S/830 PSU-E WB WH	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456531	RS342B LED27S/840 PSU-E WB WH	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
910500457072	RS342B LED19S/827 PSU-E WB WH	(0.40, 0.33)	3000 K	≥80	70.37037037037037 lm/W
910500458816	RS342B LED27S/827 PSU-E MB WH	(0.46, 0.41)	2700 K	≥80	110.63829787234043 lm/W
910500458817	RS342B LED27S/840 PSU-E MB WH	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W
910500458819	RS342B LED39S/840 PSU-E MB WH	(0.42, 0.39)	3000 K	≥90	101.2987012987013 lm/W

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
910500458884	RS342B LED17S/830 PSU-E MB WH	(0.42, 0.39)	3000 K	≥90	103.65853658536587 lm/W
910500458885	RS342B LED27S/840 PSU-E MB WH	(0.40, 0.33)	3000 K	≥80	68.35443037974683 lm/W
910500458889	RS342B LED39S/830 PSU-E MB WH	(0.43, 0.40)	3000 K	≥80	123.80952380952381 lm/W
910500458890	RS342B LED39S/840 PSU-E MB WH	(0.38, 0.38)	4000 K	≥80	120.63492063492063 lm/W
910500459011	RS342B LED17S/830 PSU-E WB WH	(0.42, 0.39)	3000 K	≥90	103.65853658536587 lm/W
910500459012	RS342B LED27S/830 PSU-E WB WH	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W
910500459013	RS342B LED39S/827 PSU-E WB WH	(0.46, 0.41)	2700 K	≥80	119.04761904761905 lm/W
910500459014	RS342B LED39S/830 PSU-E WB WH	(0.43, 0.40)	3000 K	≥80	123.80952380952381 lm/W
910500459015	RS342B LED39S/840 PSU-E WB WH	(0.38, 0.38)	4000 K	≥80	120.63492063492063 lm/W
910500459016	RS342B LED39S/840 PSU-E WB WH	(0.42, 0.39)	3000 K	≥90	101.2987012987013 lm/W

## GreenSpace Accent Elbow

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
910500459017	RS342B LED27S/ PW930 PSU-E MB WH CW-L	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W
910500459018	RS342B LED27S/ PW930 PSD- VLC-E MB WH CW-L	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W
910500459019	RS342B LED39S/ PW930 PSU-E WB WH CW-L	(0.42, 0.39)	3000 K	≥90	101.2987012987013 lm/W
910500459020	RS342B LED39S/ PW930 PSD- VLC-E WB WH CW-L	(0.42, 0.39)	3000 K	≥90	101.2987012987013 lm/W
910500465707	RS342B LED27S/ PC930 PSU-E MB WH	(0.422, 0.386)	3000 K	≥90	90 lm/W
910500465708	RS342B LED39S/	(0.422, 0.386)	3000 K	≥90	95.1219512195122 lm/W

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
	PC930 PSU-E MB WH				
910500456520	RS342B LED17S/ 830 PSU-E MB SI	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500456521	RS342B LED17S/ 840 PSU-E MB SI	(0.38, 0.38)	4000 K	≥80	125 lm/W
910500456532	RS342B LED27S/ 830 PSU-E MB SI	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456533	RS342B LED27S/ 840 PSU-E MB SI	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
910500456534	RS342B LED27S/ 830 PSU-E WB SI	(0.43, 0.40)	3000 K	≥80	114.8936170212766 lm/W
910500456535	RS342B LED27S/ 840 PSU-E WB SI	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500456512	RS342B LED17S/830 PSU-E MB BK	1700 lm	14.4 W
910500456513	RS342B LED17S/840 PSU-E MB BK	1800 lm	14.4 W
910500456514	RS342B LED17S/830 PSU-E WB BK	1700 lm	14.4 W
910500456515	RS342B LED17S/840 PSU-E WB BK	1800 lm	14.4 W
910500456524	RS342B LED27S/830 PSU-E MB BK	2700 lm	23.5 W
910500456525	RS342B LED27S/840 PSU-E MB BK	2800 lm	23.5 W
910500456526	RS342B LED27S/830 PSU-E WB BK	2700 lm	23.5 W
910500456527	RS342B LED27S/840 PSU-E WB BK	2800 lm	23.5 W
910500456516	RS342B LED17S/830 PSU-E MB WH	1700 lm	14.4 W
910500456517	RS342B LED17S/840 PSU-E MB WH	1800 lm	14.4 W
910500456518	RS342B LED17S/830 PSU-E WB WH	1700 lm	14.4 W
910500456519	RS342B LED17S/840 PSU-E WB WH	1800 lm	14.4 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500456522	RS342B LED17S/830 PSU-E WB SI	1700 lm	14.4 W
910500456523	RS342B LED17S/840 PSU-E WB SI	1800 lm	14.4 W
910500456528	RS342B LED27S/830 PSU-E MB WH	2700 lm	23.5 W
910500456529	RS342B LED27S/840 PSU-E MB WH	2800 lm	23.5 W
910500456530	RS342B LED27S/830 PSU-E WB WH	2700 lm	23.5 W
910500456531	RS342B LED27S/840 PSU-E WB WH	2800 lm	23.5 W
910500457072	RS342B LED19S/FMT PSU-E WB WH	1900 lm	27 W
910500458816	RS342B LED27S/827 PSU-E MB WH	2600 lm	23.5 W
910500458817	RS342B LED27S/PW930 PSU-E MB WH	2700 lm	25.5 W
910500458819	RS342B LED39S/PW930 PSU-E MB WH	3900 lm	38.5 W

## GreenSpace Accent Elbow

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500458884	RS342B LED17S/PW930 PSU-E MB WH	1700 lm	16.4 W
910500458885	RS342B LED27S/FMT PSU-E MB WH	2700 lm	39.5 W
910500458889	RS342B LED39S/830 PSU-E MB WH	3900 lm	31.5 W
910500458890	RS342B LED39S/840 PSU-E MB WH	3800 lm	31.5 W
910500459011	RS342B LED17S/PW930 PSU-E WB WH	1700 lm	16.4 W
910500459012	RS342B LED27S/PW930 PSU-E WB WH	2700 lm	25.5 W
910500459013	RS342B LED39S/827 PSU-E WB WH	3750 lm	31.5 W
910500459014	RS342B LED39S/830 PSU-E WB WH	3900 lm	31.5 W
910500459015	RS342B LED39S/840 PSU-E WB WH	3800 lm	31.5 W
910500459016	RS342B LED39S/PW930 PSU-E WB WH	3900 lm	38.5 W
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	2700 lm	25.5 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	2700 lm	25.5 W
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	3900 lm	38.5 W
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	3900 lm	38.5 W
910500465707	RS342B LED27S/PC930 PSU-E MB WH	2700 lm	30 W
910500465708	RS342B LED39S/PC930 PSU-E MB WH	3900 lm	41 W
910500456520	RS342B LED17S/830 PSU-E MB SI	1700 lm	14.4 W
910500456521	RS342B LED17S/840 PSU-E MB SI	1800 lm	14.4 W
910500456532	RS342B LED27S/830 PSU-E MB SI	2700 lm	23.5 W
910500456533	RS342B LED27S/840 PSU-E MB SI	2800 lm	23.5 W
910500456534	RS342B LED27S/830 PSU-E WB SI	2700 lm	23.5 W
910500456535	RS342B LED27S/840 PSU-E WB SI	2800 lm	23.5 W

### Mechanical and Housing

Order Code	Full Product Name	Color
910500456512	RS342B LED17S/830 PSU-E MB BK	Black
910500456513	RS342B LED17S/840 PSU-E MB BK	Black
910500456514	RS342B LED17S/830 PSU-E WB BK	Black
910500456515	RS342B LED17S/840 PSU-E WB BK	Black
910500456524	RS342B LED27S/830 PSU-E MB BK	Black
910500456525	RS342B LED27S/840 PSU-E MB BK	Black
910500456526	RS342B LED27S/830 PSU-E WB BK	Black
910500456527	RS342B LED27S/840 PSU-E WB BK	Black
910500456516	RS342B LED17S/830 PSU-E MB WH	White
910500456517	RS342B LED17S/840 PSU-E MB WH	White
910500456518	RS342B LED17S/830 PSU-E WB WH	White
910500456519	RS342B LED17S/840 PSU-E WB WH	White
910500456522	RS342B LED17S/830 PSU-E WB SI	White
910500456523	RS342B LED17S/840 PSU-E WB SI	White
910500456528	RS342B LED27S/830 PSU-E MB WH	White
910500456529	RS342B LED27S/840 PSU-E MB WH	White
910500456530	RS342B LED27S/830 PSU-E WB WH	White
910500456531	RS342B LED27S/840 PSU-E WB WH	White
910500457072	RS342B LED19S/FMT PSU-E WB WH	White
910500458816	RS342B LED27S/827 PSU-E MB WH	White
910500458817	RS342B LED27S/PW930 PSU-E MB WH	White
910500458819	RS342B LED39S/PW930 PSU-E MB WH	White

Order Code	Full Product Name	Color
910500458884	RS342B LED17S/PW930 PSU-E MB WH	White
910500458885	RS342B LED27S/FMT PSU-E MB WH	White
910500458889	RS342B LED39S/830 PSU-E MB WH	White
910500458890	RS342B LED39S/840 PSU-E MB WH	White
910500459011	RS342B LED17S/PW930 PSU-E WB WH	White
910500459012	RS342B LED27S/PW930 PSU-E WB WH	White
910500459013	RS342B LED39S/827 PSU-E WB WH	White
910500459014	RS342B LED39S/830 PSU-E WB WH	White
910500459015	RS342B LED39S/840 PSU-E WB WH	White
910500459016	RS342B LED39S/PW930 PSU-E WB WH	White
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	White
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	White
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	White
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	White
910500465707	RS342B LED27S/PC930 PSU-E MB WH	White
910500465708	RS342B LED39S/PC930 PSU-E MB WH	White
910500456520	RS342B LED17S/830 PSU-E MB SI	Silver
910500456521	RS342B LED17S/840 PSU-E MB SI	Silver
910500456532	RS342B LED27S/830 PSU-E MB SI	Silver
910500456533	RS342B LED27S/840 PSU-E MB SI	Silver
910500456534	RS342B LED27S/830 PSU-E WB SI	Silver
910500456535	RS342B LED27S/840 PSU-E WB SI	Silver

### Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life	Median useful life
		L80B50	L90B50
910500456512	RS342B LED17S/830 PSU-E MB BK	-	-
910500456513	RS342B LED17S/840 PSU-E MB BK	-	-

Order Code	Full Product Name	Median useful life	Median useful life
		L80B50	L90B50
910500456514	RS342B LED17S/830 PSU-E WB BK	-	-
910500456515	RS342B LED17S/840 PSU-E WB BK	-	-

## GreenSpace Accent Elbow

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910500456524	RS342B LED27S/830 PSU-E MB BK	-	-
910500456525	RS342B LED27S/840 PSU-E MB BK	-	-
910500456526	RS342B LED27S/830 PSU-E WB BK	-	-
910500456527	RS342B LED27S/840 PSU-E WB BK	-	-
910500456516	RS342B LED17S/830 PSU-E MB WH	-	-
910500456517	RS342B LED17S/840 PSU-E MB WH	-	-
910500456518	RS342B LED17S/830 PSU-E WB WH	-	-
910500456519	RS342B LED17S/840 PSU-E WB WH	-	-
910500456522	RS342B LED17S/830 PSU-E WB SI	-	-
910500456523	RS342B LED17S/840 PSU-E WB SI	-	-
910500456528	RS342B LED27S/830 PSU-E MB WH	-	-
910500456529	RS342B LED27S/840 PSU-E MB WH	-	-
910500456530	RS342B LED27S/830 PSU-E WB WH	-	-
910500456531	RS342B LED27S/840 PSU-E WB WH	-	-
910500457072	RS342B LED19S/FMT PSU-E WB WH	-	-
910500458816	RS342B LED27S/827 PSU-E MB WH	-	-
910500458817	RS342B LED27S/PW930 PSU-E MB WH	-	-
910500458819	RS342B LED39S/PW930 PSU-E MB WH	-	-
910500458884	RS342B LED17S/PW930 PSU-E MB WH	-	-
910500458885	RS342B LED27S/FMT PSU-E MB WH	-	-
910500458889	RS342B LED39S/830 PSU-E MB WH	-	-
910500458890	RS342B LED39S/840 PSU-E MB WH	-	-

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910500459011	RS342B LED17S/PW930 PSU-E WB WH	-	-
910500459012	RS342B LED27S/PW930 PSU-E WB WH	-	-
910500459013	RS342B LED39S/827 PSU-E WB WH	-	-
910500459014	RS342B LED39S/830 PSU-E WB WH	-	-
910500459015	RS342B LED39S/840 PSU-E WB WH	-	-
910500459016	RS342B LED39S/PW930 PSU-E WB WH	-	-
910500459017	RS342B LED27S/PW930 PSU-E MB WH CW-L	-	-
910500459018	RS342B LED27S/PW930 PSD-VLC-E MB WH CW-L	-	-
910500459019	RS342B LED39S/PW930 PSU-E WB WH CW-L	-	-
910500459020	RS342B LED39S/PW930 PSD-VLC-E WB WH CW-L	-	-
910500465707	RS342B LED27S/PC930 PSU-E MB WH	50000 h	25000 h
910500465708	RS342B LED39S/PC930 PSU-E MB WH	50000 h	25000 h
910500456520	RS342B LED17S/830 PSU-E MB SI	-	-
910500456521	RS342B LED17S/840 PSU-E MB SI	-	-
910500456532	RS342B LED27S/830 PSU-E MB SI	-	-
910500456533	RS342B LED27S/840 PSU-E MB SI	-	-
910500456534	RS342B LED27S/830 PSU-E WB SI	-	-
910500456535	RS342B LED27S/840 PSU-E WB SI	-	-

