



# A flexible and affordable retail toolbox

## GreenSpace Accent Fixed

With the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Fixed's regular cut-out and specific lumen packages make retrofit installation quick and easy. Completing the ideal lighting plan for your store, GreenSpace Accent Fixed offers flexible general lighting supported by a choice of beams and special light flavors and LED recipes that enable you to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Benefits

- High lumen output from very compact, low-height luminaire
- Low glare thanks to slightly recessed reflector
- Wide application coverage

### Features

- Excellent quality of light enabled by Philips PerfectAccent optics
- High energy efficiency
- Clean and robust design
- One-to-one CDM replacement

### Application

- Retail stores, especially food and fashion stores

### Specifications

<b>Type</b>	RS340B	<b>Ceiling type</b>	Exposed- and symmetrical concealed T-bar ceiling and plaster (board) ceiling
-------------	--------	---------------------	--

## GreenSpace Accent Fixed

<b>Light source</b>	Non-replaceable LED module
<b>Power</b>	1700 lm - 15 W, 2700 lm - 27 W, 3900 lm - 34.5 W at 3000 K 1900 lm - 26 W; 2600 lm - 39 W at Fresh Food Meat (FMT)
<b>Beam angle</b>	MB (24°) WB (36°) VWB (60°)
<b>Luminous flux</b>	2800, 4000 lm at 3000 K 1900, 2600 lm at FMT 2700 lm at Fresh Food Champagne (CH)
<b>Correlated Color</b>	2500 K (for CH)
<b>Temperature</b>	2700, 3000 K (for 830, PremiumWhite PW9, CrispWhite CRW, FMT) 4000 K
<b>Color Rendering Index</b>	80 for 827, 830, 840, FMT, CH 90 for PW9 >95 for CRW
<b>Median useful life L70B50</b>	70,000 hours
<b>Median useful life L80B50</b>	50,000 hours

<b>Median useful life L90B50</b>	25,000 hours
<b>Average ambient temperature</b>	+25 °C
<b>Operating temperature range</b>	+10 to +40 °C
<b>Driver</b>	Separate
<b>Mains voltage</b>	230 or 240 V / 50 - 60 Hz
<b>Dimming</b>	Non-dimmable (PSU-E) DALI-dimmable (PSD-E)
<b>Material</b>	Housing: die-cast aluminum
<b>Color</b>	White (WH, RAL9003), Black (BK, RAL 9004), Silver (SI, RAL9006)
<b>Optical cover</b>	PMMA, clear Push-in connector with pull relief (PIP), 3-pole Wieland/Adels plug (CW3), 3-pole Wieland/Adels plug with lock (CW-L)
<b>Installation</b>	Fixation by means of spring fasteners Through-wiring is possible


### Versions



### Product details



GreenSpace\_Accent\_Fixed-RS340B-DP01.tif



GreenSpace\_Accent\_Fixed-RS340B-DP02.tif

## GreenSpace Accent Fixed

### Product details

GreenSpace\_Accent\_Fixed-RS340B-  
DP03.tif



# GreenSpace Accent Fixed

## Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes (relates to presence/movement detection and daylight harvesting)

## Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

## Controls and Dimming

Dimmable	No
----------	----

## Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

## General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	F
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Product Family Code	RS340B

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Mechanical and Housing

Color	White
-------	-------

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L80B50	50000 h
Median useful life L90B50	25000 h

## General Information

Order Code	Full Product Name	Optic type
17195700	RS340B LED26S/FMT PSU-E MB II WH	MB
17196400	RS340B LED27S/830 PSU-E WB II WH	WB
17197100	RS340B LED27S/840 PSU-E WB II WH	WB
17198800	RS340B LED27S/CH PSU-E WB II WH	WB
17199500	RS340B LED27S/CRW PSU-E WB II WH	WB
17201500	RS340B LED27S/PW9 PSU-E WB II WH	WB
17212100	RS340B LED39S/840 PSU-E WB II WH	WB
17214500	RS340B LED39S/PW9 PSU-E WB II WH	WB

## Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
17195700	RS340B LED26S/FMT PSU-E MB II WH	(0.40, 0.33) SDCM<3	3000 K	≥80	67 lm/W
17196400	RS340B LED27S/830 PSU-E WB II WH	(0.43, 0.40) SDCM<3	3000 K	≥80	100 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
17197100	RS340B LED27S/840 PSU-E WB II WH	(0.38, 0.38) SDCM<3	4000 K	≥80	113 lm/W
17198800	RS340B LED27S/CH PSU-E WB II WH	(0.46, 0.39) SDCM<3	2700 K	≥80	60 lm/W

## GreenSpace Accent Fixed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
17199500	RS340B LED27S/CRW PSU-E WB II WH	(0.43, 0.40) SDCM<3	3000 K	≥90	77 lm/W
17201500	RS340B LED27S/PW9 PSU-E WB II WH	(0.42, 0.39) SDCM<3	3000 K	≥90	87 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
17212100	RS340B LED39S/840 PSU- E WB II WH	(0.38, 0.38) SDCM<3	4000 K	≥80	118 lm/W
17214500	RS340B LED39S/PW9 PSU-E WB II WH	(0.42, 0.39) SDCM<3	3000 K	≥90	100 lm/W

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
17195700	RS340B LED26S/FMT PSU-E MB II WH	2600 lm	39 W
17196400	RS340B LED27S/830 PSU-E WB II WH	2700 lm	27 W
17197100	RS340B LED27S/840 PSU-E WB II WH	2700 lm	24 W
17198800	RS340B LED27S/CH PSU-E WB II WH	2700 lm	45 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
17199500	RS340B LED27S/CRW PSU-E WB II WH	2700 lm	35 W
17201500	RS340B LED27S/PW9 PSU-E WB II WH	2700 lm	31 W
17212100	RS340B LED39S/840 PSU-E WB II WH	3900 lm	33 W
17214500	RS340B LED39S/PW9 PSU-E WB II WH	3900 lm	39 W

