



Reliable performance

Core & Coil (71A) MH ~LT~ 175W

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Avantages

- Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat
- Pre-insulated voltage leads reduce the risk of shock and shrink installation time

Fonctions

- Vacuum-pressure impregnated with a silica-filled polyester varnish
- All core and coil ballasts below 600W utilize a UL Class H (180°C) insulation system
- C and C ballasts 600W and higher utilize a UL Class N (200°C) insulation system
- Pre-insulated voltage leads
- Ballast kits supplied with pre-wired ignitor

Application

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor

Core & Coil (71A) MH ~LT~ 175W

Versions






Schéma dimensionnel



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5337510DBP	3,1 in	1,8 in	2,6 in	2,2 in	2,2 in	1,8 in
CORE & COIL HID 71A5237500DBP	2,9 in	1,5 in	2,6 in	2,2 in	2,2 in	1,8 in
CORE & COIL HID 71A5337500DBP	3,1 in	1,8 in	2,6 in	2,2 in	2,2 in	1,8 in

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A54A2500D	3,87 in	2,25 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A53A0500D	2,9 in	1,7 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A5292001D	2,88 in	1,44 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A53A0001D	2,9 in	1,7 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A5390001D	3,07 in	1,5 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A5340500DT	2,9 in	1,7 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A52A2001D	2,75 in	1,45 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A52A1500D	2,80 in	1,5 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A5181001D	2,23 in	1,18 in	3,9 in	3,5 in	2,8 in	2,4 in
CORE & COIL HID 71A5442500DT	3,92 in	2,8 in	3,9 in	3,5 in	2,8 in	2,4 in

Fonctionnement et électricité	
Fréquence d'entrée	60 Hz
Renseignements généraux	
Nombre de lampes	1 piece/unit

Fonctionnement et électricité

Order Code	Full Product Name	Tension d'entrée
192831	CORE & COIL HID MH BAL 70W M98/143	120/277/347 V
	120/277/347V KIT	

Order Code	Full Product Name	Tension d'entrée
192849	CORE & COIL HID MH BAL 100W M90/140 277V C&C	277 V

Core & Coil (71A) MH ~LT~ 175W

Order Code	Full Product Name	Tension d'entrée
192906	CORE & COIL HID MH BAL 100W M90/140 480V/120T C&C	480 V
192922	CORE & COIL HID MH BAL 100W M90/140 QUAD KIT	120/208/240/277 V
192930	CORE & COIL HID MH BAL 100W M90/140 120/277/347V KIT	120/277/347 V
189993	CORE & COIL HID MH BAL 70W M98/143 277V C&C	277 V
514794	CORE & COIL HID MH BAL 70W M98/143 QUAD KIT	120/208/240/277 V
505156	CORE & COIL HID MH BAL 100W M90/140 120/277/347V C&C	120/277/347 V

Order Code	Full Product Name	Tension d'entrée
399360	CORE & COIL HID MH BAL 150W M102/142 120/277/347V C&C	120/277/347 V
482083	CORE & COIL HID MH BAL 100W M90/140 277V C&C	277 V
482612	CORE & COIL HID MH BAL 150W M102/142 480V/120T C&C	480 V
199455	CORE & COIL HID MH BAL 50W M110 120/277V KIT	120/277 V
121079	CORE & COIL HID MH BAL 70W M139 120/277/347V C&C	120/277/347 V

Renseignements généraux

Order Code	Full Product Name	Valeur du condensateur	Type de lampe
192831	CORE & COIL HID MH BAL 70W M98/143 120/277/347V KIT	8 MFD	70W MH
192849	CORE & COIL HID MH BAL 100W M90/140 277V C&C	10 MFD	100W MH
192906	CORE & COIL HID MH BAL 100W M90/140 480V/120T C&C	10 MFD	100 MH
192922	CORE & COIL HID MH BAL 100W M90/140 QUAD KIT	12 MFD	100 MH
192930	CORE & COIL HID MH BAL 100W M90/140 120/277/347V KIT	12 MFD	100 MH
189993	CORE & COIL HID MH BAL 70W M98/143 277V C&C	8 MFD	70W MH
514794	CORE & COIL HID MH BAL 70W M98/143 QUAD KIT	8 MFD	70W MH

Order Code	Full Product Name	Valeur du condensateur	Type de lampe
505156	CORE & COIL HID MH BAL 100W M90/140 120/277/347V C&C	12 MFD	100 MH
399360	CORE & COIL HID MH BAL 150W M102/142 120/277/347V C&C	16 MFD	150 MH
482083	CORE & COIL HID MH BAL 100W M90/140 277V C&C	10 MFD	100W MH
482612	CORE & COIL HID MH BAL 150W M102/142 480V/120T C&C	16 MFD	150 MH
199455	CORE & COIL HID MH BAL 50W M110 120/277V KIT	6 MFD	50W MH
121079	CORE & COIL HID MH BAL 70W M139 120/277/347V C&C	8 MFD	70W MH

