



# Hi-Brite – ease of handling and cost reduction

## Hi-Brite

The compact, shock-resistant design of the Hi-Brite lamp series makes it easy to handle and ideal for moving head systems. Also, the compact filament ensures a high beam intensity, which can be used to reduce energy consumption: for example, 1200W can now be used instead of 2500W. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures in any burning position, which further extends lamp lifetime, reduces lamp replacement costs and ensures consistency of high-quality light output.

### 优点

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Easy handling, ideal for moving head systems
- High beam intensity resulting in reduced energy consumption (1200W instead of 2500W)

### 特点

- Philips Pinch Protection
- Compact, shock resistant design
- Compact filament


### 应用

- Studio and film lighting
- Stage and theatre lighting
- Touring and show lighting

Versions



二维绘图



Product	D (max)	H	W	L	C (max)
6980Z 1200W G22 80V 10PK	25 mm	10.2 mm	11.7 mm	63.5 mm	140 mm

