



Faro – For both contemporary and modern environments

Faro Poles and brackets

With Faro product range, you have the freedom to create customized installations, historic or more contemporary in inspiration, which suits beautifully in urban areas. The traditional style of this product family, with simple linear and understated interpretations has been designed to enrich the atmosphere in your environments. Faro family offers different brackets configurations which allow you to customize your complete set and adapt your luminaire to your preference

Benefits

- Design inspired by historical theme which allows the environment they are part of to be accentuated or enhanced
- Complete poles and brackets offer
- Luminaires can be mounted suspended or post top

Features

- Brackets available in three outreaches for wall or pole mounting versions
- The Faro top mounting version is available for post top mounting luminaire while the Faro pole mounting version is designed for the Faro brackets
- Poles height range from 3,5m to 5m

Application

- Urban and architectural areas
- Square and parks
- City Centres

Faro Poles and brackets

Versions



FARO APPLIQUE POLE 5M50



FARO SINGLE ARM BRACKET S400



FARO SINGLE ARM BRACKET S700







FARO SINGLE ARM BRACKET S900




YHM702 FARO POLE 5M

Dimensional drawing



Faro Poles and brackets

Dimensional drawing



General Information

Order Code	Full Product Name	Accessory color	CE mark	Product family code
912300023382	YHM700 PL-FLG 4700 90 BK PD-T 2x2xM8-430	Black	-	YHM700
912300023384	YHM700 PL-FLG 4700 90 BK PD-T 2x2xM8-430	Black	-	YHM700
912300023383	YHM700 PL-FLG 5500 90 BK PD-T 2x2xM8-430	Black	-	YHM700
912300023385	YHM700 PL-FLG 5500 90 BK PD-T 2x2xM8-430	Black	-	YHM700

Order Code	Full Product Name	Accessory color	CE mark	Product family code
912300023378	JGP700 MBP/MBW 400 BK G1	-	Yes	JGP700
912300023379	JGP700 MBP 700 BK G1	-	Yes	JGP700
912300023380	JGP700 MBP 900 BK G1	-	Yes	JGP700
912300023390	YHM702 PL-FLG 5000 60 BK PD-T	Black	-	YHM700

