



# For reliable unveiling of secrets

## TL Blacklight Blue

TL/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Benefits

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

### Features

- Straight outer envelope

### Application

- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theaters, and sign lighting


# TL Blacklight Blue

## Versions



TL Blacklight Blue T38 G13

## Dimensional drawing



| Product              | D (max) | A (max)   | B (max)   | B (min)   | C (max)   |
|----------------------|---------|-----------|-----------|-----------|-----------|
| F40T12/BLACKLIGHT/48 | 40.5 mm | 1199.4 mm | 1206.5 mm | 1204.1 mm | 1213.6 mm |
| BLB LF               |         |           |           |           |           |

