



Product Description

Softone Globe

Decorative covered energy-saving lamps for consumer applications

Benefits

- High energy efficiency (European energy efficiency labelling class B)
- Reduced glare and aesthetic form due to globe shaped outer bulb

Features

- Long-life alternative to incandescent lamps
- Light output after 1 minute 80%
- Almost constant light output (>90%) over recommended temperature range

Application

- Designed for incandescent lamp replacement in (open) luminaires with a decorative function or as replacement of globe incandescent lamps
- Especially suitable for applications with a decorative function in areas where lighting is required for longer periods of time or where lamp replacement is difficult
- Ambient temperature range -10 to +55°C (base-up), +5 to +55°C (base-down)
- Enclosed fixtures are required for outdoor applications
- Not suitable for dimming and electronic devices


Softone Globe

Versions



E27 G120

Dimensional drawing



Product	C (max)	F (max)
Softone Globe 23W CDL E27 G120 1CH/4	182 mm	48.2 mm

