



PL-S is a low wattage compact fluorescent lamp

PL-S consumer products

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming.

Vorteile

- Reliable and hassle free
- Good color rendering (CRI >80)

Merkmale

- 2-pin base with a housing incorporating the special instant starter
- Low light depreciation over lamp life
- Long life performance

Anwendung

- Suitable for luminaire specially designed for PL-S 2 pin lamps which can include downlighters, wall units, table and desk lamps, pendant lamps and outdoor lighting.

Hinweise

- Es ist sehr unwahrscheinlich, dass der Glasbruch einer Lampe negative Auswirkungen auf Ihre Gesundheit hat. Wenn es zu einem Glasbruch kommt, lüften Sie den Raum 30 Minuten lang und entfernen Sie die Splitter möglichst mit Handschuhen. Legen Sie die Splitter in eine verschließbaren Plastikbeutel und geben Sie ihn beim Werkstoffhof zum Recycling ab. Benutzen Sie keinen Staubsauger.


PL-S consumer products

Versions



GLIM2012503 Wioleta Sadowska

Abmessungsskizzen



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 9W/827/2P 1PP/10	28 mm	13 mm	129 mm	145 mm	167 mm

