



PL-S is a low wattage compact fluorescent lamp

PL-S consumer products

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming.

Vorteile

- Reliable and hassle free
- Good color rendering (CRI >80)

Merkmale

- 2-pin base with a housing incorporating the special instant starter
- Low light depreciation over lamp life
- Long life performance

Anwendung


- Suitable for luminaire specially designed for PL-S 2 pin lamps which can include downlighters, wall units, table and desk lamps, pendant lamps and outdoor lighting.

PL-S consumer products

Versions



Abmessungsskizzen



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 9W/827/2P 1PP/10	28 mm	13 mm	129 mm	145 mm	167 mm

