



PL-S is a low wattage compact fluorescent lamp

PL-S consumer products

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming.

Faydaları

- Reliable and hassle free
- Good color rendering (CRI >80)

Özellikler

- 2-pin base with a housing incorporating the special instant starter
- Low light depreciation over lamp life
- Long life performance

Uygulama


- Suitable for luminaire specially designed for PL-S 2 pin lamps which can include downlighters, wall units, table and desk lamps, pendant lamps and outdoor lighting.

Güvenlik ve uyarılar

- Lamba kırılmasının sağlığını üzerinde herhangi bir olumsuz etkisi olmayacağını söylemek pek de mümkün değildir. Bir lamba kırıldığında, odayı 30 dakika süreyle havalandırın ve kırık parçaları tercihen eldiven kullanarak toplayın. Bunları ağız kapalı bir plastik torbaya koyun ve geri dönüşüm için size en yakın atık toplama merkezine götürün. Elektrikli süpürge kullanmayın.

PL-S consumer products

Boyutlu çizim



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-S 9W/827/2P 1PP/10	28 mm	13 mm	129 mm	145 mm	167 mm
PL-S 7W/827/2P 1PP/10	28 mm	13 mm	97 mm	113 mm	135 mm
PL-S 11W/827/2P 1PP/10	28 mm	13 mm	198 mm	214 mm	235,8 mm

