



Energy Saving Lamp combines superior performance with soft warm light and traditional bulb design

MASTER Softone

Energy Saving lamps with design and superior performance, designed for incandescent lamp replacement in professional applications (Hotels, restaurants, etc), where you want to create an intimate and cozy atmosphere. With a comprehensive range of wattages, it enables easy replacement of most incandescent lamp all the way

Benefits

- Light quality and distribution similar to the opalised incandescent lamps
- Gives a soft, diffused light with a high comfort level
- Save your money with long life-time and high energy efficiency compare to incandescent lamp

Features

- Professional long-life energy saving alternative to incandescent lamps
- Flicker-free start
- Almost constant light output (>90%) over recommended temperature range 0 to +50°C

Application


- Designed for incandescent lamp replacement in professional applications (hotels, restaurants), where you want to create an intimate and cosy atmosphere; suitable for applications where lamp is visible
- Enclosed fixtures are required for outdoor applications
- Not suitable for use with dimmers or electronic gear

Versions



23W E27 A75 Erp

Dimensional drawing



Product	D (max)	C (max)	F (max)
Master Softone 23W WW E27 220-240V 1PF/6	75.8 mm	162.6 mm	48.1 mm

