



# Small size fluorescent lamp

## TL Mini consumer products

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

### Výhody

- Long lifetime
- Energy saving
- Color /827 radiates light which is comparable with incandescent lighting

### Vlastnosti

- Small diameter tubes

### Aplikace

- TL Mini /827 (warm white) is ideal for applications where better color rendering and efficacy (than standard colors) are required like e.g. halls, staircase lighting in apartment buildings, kitchens, mirror, cabinet and cupboard lighting.
- TL Mini Standard color is suitable for applications where color rendering is less important like orientation and emergency lighting.

## TL Mini consumer products

### Versions



### Rozměrové výkresy

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 13W/33-640 1PP/10	16 mm	516,9 mm	524,0 mm	521,6 mm	531,1 mm

