



Small size fluorescent lamp

TL Mini consumer products

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Előnyök

- Long lifetime
- Energy saving
- Color /827 radiates light which is comparable with incandescent lighting

Szolgáltatások

- Small diameter tubes

Alkalmazás

- TL Mini /827 (warm white) is ideal for applications where better color rendering and efficacy (than standard colors) are required like e.g. halls, staircase lighting in apartment buildings, kitchens, mirror, cabinet and cupboard lighting.
- TL Mini Standard color is suitable for applications where color rendering is less important like orientation and emergency lighting.

Figyelmeztetések és biztonság

- Nagyon valószínűtlen, hogy egy lámpa eltörése károsítaná az egészségét. Ha eltörik egy lámpa, szellőztesse a szobát 30 percig, és cserélje ki az alkatrészt, lehetőleg kesztyűben. Tegye a törött lámpát lezárt műanyag zacskóba, és vigye a helyi hulladékfeldolgozóba újrahasznosításra. Ne használjon porszívót.

TL Mini consumer products

Versions

