



Mains-voltage linear R7S with very high light output

CorePro LEDlinear MV

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light that is just like a halogen lamp. Within the range, you can choose dimmable products which have deep a dimming function that enables a cosy ambience when using a dimmable fixture.

Benefits

- Up to 90% energy saving compared to standard halogen lamps
- Lower maintenance costs

Features

- Easy retrofit
- Operates at 220-240 V AC and its form-factor is designed as a direct retrofit into all double-ended holders
- Lifetime of 15,000 hours (B50L70)
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS compliant

Application

- Living rooms, corridors, outdoor luminaires (security lighting), free floor-standing indoor luminaires, construction lighting

CorePro LEDlinear MV

Versions



R7S CL

Dimensional drawing

C

Product	D	C
CorePro LED linear R7S 118mm 6.5-60W 830	22.5 mm	118 mm



