



# Vaya Linear LP – Ultra compact exterior-rated line-voltage linear LED grazing luminaire for dynamic color-changing and crisp white lighting effects

## Vaya Linear LP

Vaya Linear LP is a super slim outdoor linear luminaire for low-level grazing applications, with wide 120° beam or elliptical 28° x 84° optics. Its slim form factor is ideal for space-restricted applications with limited setback or allowable install height. The robust Vaya Linear LP offers a variety of color and white CCT options with either static on/off- or dynamic control options via standard DMX-512. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

### Benefits

- Suitable for space-restricted and low-profile applications (indoor and outdoor)
- Fast and easy installation
- Allows low-level grazing or exterior cove lighting applications

# Vaya Linear LP

## Features

- Reliable, cost-effective LED lighting luminaire
- Slim outdoor IP66-rated housing and connectors
- Available with 28 x 84° or 120° beams
- DMX512 control (RGB version)

## Application

- Exterior cove lighting
- Low-level grazing

## Specifications

<b>Type</b>	BCP421 (RGB version)
	BCP422 (white light version)
	BCP423 (mono-color light version)
<b>Light source</b>	Built-in LED-module
<b>Power</b>	14 or 28 W (RGB)
	10 or 20 W (3000K and 4000 K)
<b>Beam angle</b>	28 x 84 or 120°
<b>Luminous flux</b>	300 or 600 lm (RGB)
	600 or 1200 lm (3000 K and 4000 K)
<b>Luminaire efficacy</b>	62 lm/W
<b>Correlated Color</b>	2700, 3000, 4000 or 5000 K
<b>Temperature</b>	Red, green, blue, amber, RGB
<b>Color Rendering Index</b>	80 (for 4000 K)
<b>Maintenance of lumen output - L70</b>	60,000 hours at 25 °C

<b>Operating temperature range</b>	-40 to +40 °C
<b>Driver</b>	Integrated
<b>Mains voltage</b>	100-240 VAC / 50-60 Hz
<b>Controls system input</b>	DMX control for RGB versions
<b>Optic</b>	Elliptical or wide beam
<b>Optical cover</b>	Glass, flat
<b>Material</b>	Housing: extruded aluminum, anodized finish
	Cover: clear tempered glass
<b>Color</b>	Grey, anodized
<b>Connection</b>	Push-in connector
<b>Installation</b>	Surface mounting
	Location adjustable and tilting surface-mounting bracket

## Versions

Vaya Linear LP BCP421/422/423  
floodlight, 0.6 m, wide beam



Vaya Linear LP BCP421/422/423  
floodlight, 0.6 m, elliptical beam



Vaya Linear LP BCP421/422/423  
floodlight, 1.2 m, wide beam



Vaya Linear LP BCP421/422/423  
floodlight, 1.2 m, elliptical beam



Product details

Combined power and data connector



Open-wire connection



Inter-fixture connection, 300 mm/1 ft spacing



Adjacent inter-fixture connection



Accessories

Leader cable for white version, 15 m

Ordercode 912400130044



Ordercode 912400130045,  
912400130048, 912400130049,  
912400130051, 912400130054



Jumper cable for white version, 1,5 m

Ordercode 912400130046



Leader cable for RGB version, 15 m

Ordercode 912400130047



Accessories

Glare shield

Ordercode 912400130180,  
912400130181



Ordercode 912400134844



Ordercode 912400134845

