



# Vaya Linear MP – reliable, cost-effective LED linear fixture

## Vaya Linear MP

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colorful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

### Benefits

- Economical solution
- Suitable for harsh outdoor environments requiring relatively high light output
- Fast and easy installation

### Features

- IP66-rated housing and connectors
- Relatively high light output
- Available with 10 x 50 or 50° beams
- Auto-ranging 100-277 V, 50/60 Hz input
- DMX512 control (RGB version)
- Dedicated connectors for quick, easy and secure installation

### Application

- Grazing lighting of monuments, bridges, shops, hotels

### Specifications

Type	BCP424 (RGB version)
	BCP425 (white light version)
	BCP426 (mono-color light version)

Light source	Built-in LED-module
Power	18-60 W
Beam angle	10 x 50 and 50°

## Vaya Linear MP

<b>Luminous flux</b>	450-1800 lm (RGB)
	840-3360 lm (white light)
<b>Luminaire efficacy</b>	50 lm/W
<b>Correlated Color</b>	3000 or 4000 K
<b>Temperature</b>	RGB
<b>Color Rendering Index</b>	80
<b>Maintenance of lumen output - L70</b>	50,000 hours at 25°C
<b>Operating temperature range</b>	-40 to +40 °C
<b>Driver</b>	Integrated

<b>Mains voltage</b>	100-277 V / 50-60 Hz
<b>Controls system input</b>	DMX control for RGB versions
<b>Optic</b>	Asymmetrical or wide beam
<b>Optical cover</b>	Glass, transparent
<b>Material</b>	Housing: extruded aluminum
	Cover: glass, tempered
<b>Color</b>	Gray, RAL7043
<b>Connection</b>	Daisy-chain power input and output connectors
<b>Installation</b>	Surface mounting
	Location adjustable and tilting surface-mounting bracket
<b>Remarks</b>	Leader cables and jumper cables should be ordered separately

## Versions

Vaya Linear MP BCP424/425/426  
floodlight, 0.3 m



Vaya Linear MP BCP424/425/426  
floodlight, 1.2 m



## Accessories

Leader cable for white version, 15 m

Ordercode 912400130044



Jumper cable for white version, 1,5 m

Ordercode 912400130046

