



# Vaya Linear MP – reliable, cost-effective LED linear fixture

## Vaya Linear MP

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colourful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

### Benefits

- Economical solution
- Suitable for harsh outdoor environments requiring relatively high light output
- Fast and easy installation

### Features

- IP66-rated housing and connectors
- Relatively high light output
- Available with 10 x 50 or 50° beams
- Auto-ranging 100-277 V, 50/60 Hz input
- Dedicated connectors for quick, easy and secure installation

### Application

- Grazing lighting of monuments, bridges, shops, hotels

### Specifications

Type	BCP424 (RGB version)
	BCP425 (white light version)
	BCP426 (mono-colour light version)
Light source	Built-in LED module

Power	18 W / 60 W
Beam angle	10 x 50 and 50°
Luminous flux	450-1,800 lm (RGB)
	840-3,400 lm (white light)

# Vaya Linear MP

Luminaire efficacy	50 lm/W
Correlated Colour	3,000 or 4,000 K (2,700 K and 5,000 K custom options)
Temperature	RGB
Colour Rendering Index	78
Maintenance of lumen output – L70	60,000 hours at 25 °C
Operating temperature range	-40 to +40 °C
Driver	Integrated
Mains voltage	100-277 VAC/ 50-60 Hz

Control system input	DMX control for RGB versions
Optic	Asymmetrical or wide beam
Optical cover	Glass, transparent
Material	Housing: extruded aluminium Cover: glass, tempered
Colour	Grey, RAL7043
Connection	Daisy-chain power input and output connectors
Installation	Surface mounting Location-adjustable and tilting surface-mounting bracket
Remarks	Extension leads and jump leads should be ordered separately

## Versions



## Accessories

Leader cable for RGB version, 15 m

Ordercode 912400130047

