



# Vaya Linear MP – reliable, cost-effective LED linear fixture

## Vaya Linear MP

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colourful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

### Benefits

- Economical solution
- Suitable for harsh outdoor environments requiring relatively high light output
- Fast and easy installation

### Features

- IP66-rated housing and connectors
- Relatively high light output
- Available with 10 x 50 or 50° beams
- Auto-ranging 100-277 V, 50/60 Hz input
- Dedicated connectors for quick, easy and secure installation

### Application

- Grazing lighting of monuments, bridges, shops, hotels

### Specifications

<b>Type</b>	BCP424 (RGB version)	<b>Power</b>	18 W / 60 W	
	BCP425 (white light version)		<b>Beam angle</b>	10 x 50 and 50°
	BCP426 (mono-colour light version)			<b>Luminous flux</b>
<b>Light source</b>	Built-in LED module		840-3,400 lm (white light)	

## Vaya Linear MP

<b>Luminaire efficacy</b>	50 lm/W
<b>Correlated Colour</b>	3,000 or 4,000 K (2,700 K and 5,000 K custom options)
<b>Temperature</b>	RGB
<b>Colour Rendering Index</b>	78
<b>Maintenance of lumen output – L70</b>	60,000 hours at 25 °C
<b>Operating temperature range</b>	-40 to +40 °C
<b>Driver</b>	Integrated
<b>Mains voltage</b>	100-277 VAC/ 50-60 Hz

<b>Control system input</b>	DMX control for RGB versions
<b>Optic</b>	Asymmetrical or wide beam
<b>Optical cover</b>	Glass, transparent
<b>Material</b>	Housing: extruded aluminium Cover: glass, tempered
<b>Colour</b>	Grey, RAL7043
<b>Connection</b>	Daisy-chain power input and output connectors
<b>Installation</b>	Surface mounting Location-adjustable and tilting surface-mounting bracket
<b>Remarks</b>	Extension leads and jump leads should be ordered separately

## Versions

Vaya Linear MP BCP424/425/426  
floodlight, 0.3 m



Vaya Linear MP BCP424/425/426  
floodlight, 1.2 m



## Accessories

Leader cable for white version, 15 m

Ordercode 912400130044



Jumper cable for white version, 1,5 m

Ordercode 912400130046



Leader cable for RGB version, 15 m

Ordercode 912400130047



Jumper cable for RGB version, 1,5 m

Ordercode 912400130049



