



C-Splash 2 – submersible, colour- changing LED spotlight for use in fresh and salt water

C-Splash 2

C-Splash 2 is an ultra-thin, submersible fixture designed to provide vibrant colour and colour-changing light in fresh and saltwater locations to a depth of 4.6 meters. With its watertight cast brass housing and silicon bronze adjusting hardware, C-Splash 2 is perfect for water-based applications such as fountains and theme park installations, as well as for applications situated in harsh environments.

Benefits

- Rugged and watertight; extremely low-maintenance
- Choice of beam angles and light positioning
- Compatible with industry-leading controls

Features

- Long-life LEDs delivering RGB colours and light output of over 500 lumens
- IP68-rated: also able to withstand water treated with bromine or chlorine
- 10° clear glass lens for extended light projection and 22° frosted tempered glass lens for a soft-edge beam
- Locking base and pivot allows vertical and horizontal rotation through full 360°
- Works with complete Philips line of controllers, as well as third-party DMX controllers

C-Splash 2

Application

- Water-based applications
- Harsh environments

Versions



LED svítidlo C-Splash 2 BCP468
pro použití pod vodou

