



# Submersible spotlight with intelligent RGB light

## C-Splash 2

C-Splash 2 is an ultra-thin, submersible luminaire designed to provide vibrant color and color-changing light in water to a depth of 4.6 m (15 ft). With its watertight cast brass housing and silicon bronze adjusting hardware, C-Splash 2 is perfect for water-based applications such as fountains and theme park installations, as well as for applications situated in harsh environments.

### Benefits

- Rugged and watertight
- Extremely low-maintenance
- Choice of beam angles and light positioning
- Compatible with industry-leading controls

### Features

- Long-life LEDs delivering RGB colors and light output of over 500 lumens
- IP68-rated: also able to withstand water treated with bromine or chlorine
- 10° clear glass lens for extended light projection and 22° frosted tempered glass lens for a soft-edge beam
- Locking base and pivot allows vertical and horizontal rotation through full 360°
- Works with complete Color Kinetics line of controllers, as well as third-party DMX controllers

### Application

- Water-based applications
- Harsh environments

## C-Splash 2

### Versions



C-Splash 2 BCP468 LED fixture for  
underwater applications

