



Graze MX Powercore – high-intensity illumination of multi- storey façades and surfaces

eW Graze MX Powercore

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features

- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

Application

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

Versions



eW Graze Powercore BCS419,
svítidlo pro architektonické
osvětlení, 305 mm



eW Graze Powercore BCS419,
svítidlo pro architektonické
osvětlení, 24 LED, 609 mm



eW Graze Powercore BCS419,
svítidlo pro architektonické
osvětlení, 914 mm



eW Graze Powercore BCS419,
svítidlo pro architektonické
osvětlení, 36 LED, 1219 mm



eW Graze Powercore BCS419,
architektonické osvětlení, 305 mm



eW Graze Powercore BCS419,
architektonické osvětlení, 609 mm



eW Graze Powercore BCS419,
architektonické osvětlení, 914 mm



eW Graze Powercore BCS419,
architektonické osvětlení, 1219 mm

Product details



OPDP_BCS419i_0001-Detail photo



OPDP_BCS419i_0005-Detail photo



OPDP_BCS419i_0007-Detail photo



OPDP_BCS419i_0011-Detail photo



Graze Powercore, 305 mm (1 ft)



Graze Powercore, Input Connection



eW Graze MX Powercore

Product details



Graze Powercore, Output Connection



Graze Powercore, 610 mm (2 ft)



Graze Powercore, 914 mm (3 ft)



Graze Powercore, 1219 mm (4 ft)

