



# Premium exterior linear grazing luminaire with single temperature white light

## eW Graze MX Powercore

eW Graze MX Powercore is a high-performance, exterior linear luminaire that features the most light output in our line of solid white light grazing luminaires. It is designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze Essential White luminaires offer a single channel of white light. Available in 2700 K, 3000 K, 3500 K, 4000 K, and 5500 K. Multiple luminaire lengths, beam angles, output levels, and power consumption levels support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

### Benefits

- Superior light quality, consistency and output thanks to Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Color Kinetics controllers

## Features

- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

## Application

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

## Versions



eW Graze Powercore BCS419  
architectural lighting fixture, 305  
mm



eW Graze Powercore BCS419  
architectural lighting fixture with  
24 LEDs, 609 mm



eW Graze Powercore BCS419  
architectural lighting fixture, 914  
mm



eW Graze Powercore BCS419  
architectural lighting fixture with  
36 LEDs, 1219 mm



eW Graze Powercore BCS419  
architectural lighting, 305 mm



eW Graze Powercore BCS419  
architectural lighting, 609 mm

eW Graze MX Powercore

Versions

eW Graze Powercore BCS419  
architectural lighting, 914 mm



eW Graze Powercore BCS419  
architectural lighting, 1219 mm



Product details

OPDP\_BCS419i\_0001-Detail  
photo



OPDP\_BCS419i\_0005-Detail  
photo



OPDP\_BCS419i\_0007-Detail  
photo



OPDP\_BCS419i\_0011-Detail photo



eW Graze MX Powercore

Product details

Graze Powercore, 305 mm (1 ft)



Graze Powercore, Input Connection



Graze Powercore, Output Connection



Graze Powercore, 610 mm (2 ft)



Graze Powercore, 914 mm (3 ft)



Graze Powercore, 1219 mm (4 ft)

