



# Graze QLX Powercore – medium-intensity illumination of multi- storey facades and surfaces

## eW Graze QLX Powercore

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

### Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

### Features

- Medium-intensity exterior-rated linear LED luminaire with output comparable to first-generation product at lower power consumption
- Consistent output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

## eW Graze QLX Powercore

### Application

- Illumination of exterior facades and structures
- Illumination of moderate architectural details
- Signage and flood-/wash-lighting applications (depending on beam angle)

### Versions

Graze QLX Powercore, svítidlo pro  
architektonické osvětlení



Graze QLX Powercore, svítidlo pro  
architektonické osvětlení



Graze QLX Powercore  
architectural lighting fixture



Graze QLX Powercore, svítidlo pro  
architektonické osvětlení



### Product details



Male connection



Female connection

Product details



Side view of all four lengths in family

Graze Powercore, 305 mm (1 ft)



Graze Powercore, Input Connection



Graze Powercore, Output Connection

Graze Powercore, 610 mm (2 ft)



Graze Powercore, 914 mm (3 ft)



Graze Powercore, 1219 mm (4 ft)



