



eW Graze EC Powercore – exterior cove, niche and detail illumination

eW Graze EC Powercore

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features

- Soft-edged light output for volume-fill applications thanks to diffuse cover lens
- Low power consumption is perfect for less demanding exterior applications
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

Application

- Illumination of exterior coves
- Illumination of exterior details (porte-cochères, mullions, balustrades, etc.)

Versions



ColorGraze EC Powercore BCS428
– svítidlo pro architektonické
osvětlení (RGB, 305 mm)



ColorGraze CE Powercore BCS428
architectural lighting fixture (RGB,
609 mm)



ColorGraze EC Powercore BCS428
architectural lighting fixture (RGB,
914 mm)



ColorGraze EC Powercore BCS428
architectural lighting fixture (RGB,
1219 mm)



Graze EC Powercore, svítidlo pro
architektonické osvětlení



Graze EC Powercore, svítidlo pro
architektonické osvětlení



Graze EC Powercore, svítidlo pro
architektonické osvětlení



Graze EC Powercore architectural
lighting fixture

Product details



OPDP_BCS428i_0001-Detail
photo



OPDP_BCS428i_0005-Detail
photo

Graze Powercore, 305 mm (1 ft)



Graze Powercore, Input
Connection

Graze Powercore, Output
Connection



Graze Powercore, 610 mm (2 ft)

Graze Powercore, 914 mm (3 ft)



eW Graze EC Powercore

Product details

Graze Powercore, 1219 mm (4 ft)

