



# eW Graze EC Powercore – exterior cove, niche and detail illumination

## eW Graze EC Powercore

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

### Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

### Features

- Soft-edged light output for volume-fill applications thanks to diffuse cover lens
- Low power consumption is perfect for less demanding exterior applications
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

### Application

- Illumination of exterior coves
- Illumination of exterior details (porte-cochères, mullions, balustrades, etc.)

eW Graze EC Powercore

Versions

ColorGraze EC Powercore BCS428  
– svítidlo pro architektonické  
osvětlení (RGB, 305 mm)



Product details

OPDP\_BCS428i\_0001-Detail  
photo



OPDP\_BCS428i\_0005-Detail  
photo



Graze Powercore, 305 mm (1 ft)



Graze Powercore, Input  
Connection



Graze Powercore, Output  
Connection



eW Graze EC Powercore

Product details

Graze Powercore, 610 mm (2 ft)



Graze Powercore, 914 mm (3 ft)



Graze Powercore, 1219 mm (4 ft)

