



# **iW Graze MX Powercore – high- intensity illumination of multi-storey façades and surfaces**

## **iW Graze MX Powercore**

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

### **Benefits**

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

### **Features**


- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

# iW Graze MX Powercore

## Application

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

## Versions



## Product details

