



Graze MX Powercore – high-intensity illumination of multi- storey façades and surfaces

eColor Graze MX Powercore

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Beneficios

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Características

- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

eColor Graze MX Powercore

Aplicaciones

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

Especificaciones

Type	BCS439
Light source	Build-in LED-module
Power (+/-10%)	15, 30, 45, 60 W
Beam angle	9, 10 x 60, 15 x 30, 30 x 60, 60 x 30°
Maintenance of lumen output - L70F10	60,000 hours at 25 °C
Operating temperature range	-40 to +50 °C
Driver	Integrated

Mains voltage	100-277 V AC / 50-60 Hz
Dimming	ELV dimmers
Optic	Narrow, medium or wide beam, rotational beam angle
Optical element	Micro lens optic in polycarbonate cover
Material	Housing: aluminum, extruded Lens: polycarbonate
Color	Grey
Connection	Push-in connector with 3 poles
Installation	Multi-positional, constant torque, locking hinges

Versions

eColor Graze Powercore BCS439
architectural lighting fixture, 305 mm



eColor Graze Powercore BCS439
architectural lighting fixture, 609 mm




eColor Graze Powercore BCS439
architectural lighting fixture, 914 mm



eColor Graze Powercore BCS439
architectural lighting fixture, 1219 mm



Plano de dimensiones



Product	A	B
BCS439 9 RD L609	439 mm	610 mm
BCS439 9 AM L914	744 mm	914 mm
BCS439 30x60 GN L305	134 mm	305 mm
BCS439 30x60 GN L609	439 mm	610 mm
BCS439 10x60 BL L609	439 mm	610 mm
BCS439 9 AM L609	439 mm	610 mm
BCS439 10x60 RD L914	744 mm	914 mm
BCS439 60x30 BL L1219	1049 mm	1219 mm
BCS439 9 AM L305	134 mm	305 mm
BCS439 9 RD L305	134 mm	305 mm
BCS439 60x30 RD L305	134 mm	305 mm
BCS439 10x60 RD L609	439 mm	610 mm
BCS439 15x30 BL L609	439 mm	610 mm
BCS439 9 GN L1219	1049 mm	1219 mm
BCS439 15x30 BL L914	744 mm	914 mm
BCS439 15x30 GN L1219	1049 mm	1219 mm
BCS439 15x30 BL L1219	1049 mm	1219 mm
BCS439 60x30 GN L914	744 mm	914 mm
BCS439 10x60 GN L305	134 mm	305 mm
BCS439 10x60 BL L305	134 mm	305 mm
BCS439 10x60 GN L1219	1049 mm	1219 mm
BCS439 10x60 BL L914	744 mm	914 mm
BCS439 15x30 RD L1219	1049 mm	1219 mm
BCS439 9 GN L609	439 mm	610 mm
BCS439 9 BL L914	744 mm	914 mm
BCS439 9 AM L1219	1049 mm	1219 mm
BCS439 30x60 RD L1219	1049 mm	1219 mm
BCS439 9 RD L914	744 mm	914 mm
BCS439 60x30 AM L914	744 mm	914 mm
BCS439 30x60 BL L914	744 mm	914 mm
BCS439 60x30 AM L609	439 mm	610 mm
BCS439 30x60 RD L305	134 mm	305 mm
BCS439 15x30 RD L609	439 mm	610 mm
BCS439 15x30 AM L305	134 mm	305 mm
BCS439 9 BL L609	439 mm	610 mm
BCS439 15x30 AM L1219	1049 mm	1219 mm
BCS439 60x30 GN L1219	1049 mm	1219 mm
BCS439 60x30 GN L609	439 mm	610 mm
BCS439 15x30 AM L914	744 mm	914 mm
BCS439 30x60 GN L1219	1049 mm	1219 mm
BCS439 60x30 GN L305	134 mm	305 mm
BCS439 10x60 RD L1219	1049 mm	1219 mm
BCS439 60x30 AM L1219	1049 mm	1219 mm
BCS439 15x30 RD L914	744 mm	914 mm
BCS439 9 RD L1219	1049 mm	1219 mm
BCS439 15x30 RD L305	134 mm	305 mm
BCS439 60x30 BL L914	744 mm	914 mm
BCS439 15x30 BL L305	134 mm	305 mm
BCS439 30x60 AM L609	439 mm	610 mm
BCS439 10x60 RD L305	134 mm	305 mm

Plano de dimensiones

Product	A	B
BCS439 10x60 GN L914	744 mm	914 mm
BCS439 60x30 BL L305	134 mm	305 mm
BCS439 60x30 BL L609	439 mm	610 mm
BCS439 60x30 AM L305	134 mm	305 mm
BCS439 15x30 GN L305	134 mm	305 mm
BCS439 10x60 AM L305	134 mm	305 mm
BCS439 15x30 AM L609	439 mm	610 mm
BCS439 30x60 AM L914	744 mm	914 mm
BCS439 30x60 AM L1219	1049 mm	1219 mm
BCS439 30x60 GN L914	744 mm	914 mm
BCS439 9 GN L914	744 mm	914 mm
BCS439 15x30 GN L609	439 mm	610 mm
BCS439 10x60 GN L609	439 mm	610 mm
BCS439 30x60 BL L1219	1049 mm	1219 mm
BCS439 9 GN L305	134 mm	305 mm
BCS439 60x30 RD L914	744 mm	914 mm
BCS439 30x60 BL L609	439 mm	610 mm
BCS439 60x30 RD L609	439 mm	610 mm
BCS439 30x60 RD L914	744 mm	914 mm
BCS439 9 BL L305	134 mm	305 mm
BCS439 60x30 RD L1219	1049 mm	1219 mm
BCS439 10x60 AM L609	439 mm	610 mm
BCS439 30x60 AM L305	134 mm	305 mm
BCS439 9 BL L1219	1049 mm	1219 mm
BCS439 10x60 AM L1219	1049 mm	1219 mm
BCS439 30x60 RD L609	439 mm	610 mm
BCS439 15x30 GN L914	744 mm	914 mm
BCS439 10x60 AM L914	744 mm	914 mm
BCS439 10x60 BL L1219	1049 mm	1219 mm
BCS439 30x60 BL L305	134 mm	305 mm

Detalles del producto

Male connection



Female connection



Detalles del producto

Side view of all four lengths in family



Accesorios

Image
not yet
available

Terminator, set of 10 pieces

Ordercode 910503700580

Graze Glare Shield, 305 mm

Ordercode 910503700745



Graze Glare Shield, 610 mm

Ordercode 910503700746



Graze Glare Shield, 915 mm

Ordercode 910503700747



Graze Glare Shield, 1220 mm

Ordercode 910503700748



Graze Mounting Hinge

Ordercode 910503700772



Accesorios



Leader cable, 1525 mm

Ordercode ,



Leader cable, 3050 mm

Ordercode 910503704067



Leader cable, 3050 mm

Ordercode 910503704072



Jumper cable

Ordercode 910503704074



Jumper cable, 1525 mm

Ordercode 910503704080



Jumper cable, 305 mm

Ordercode 910503704077



Jumper cable, 3050 mm

Ordercode 910503704083

