



Color Graze QLX Powercore – medium- intensity illumination of multi-storey facades and surfaces

ColorGraze QLX Powercore

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze QLX Powercore is capable of illuminating over 10 metres at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features

- Medium-intensity exterior-rated linear LED luminaire with output comparable to first-generation product at lower power consumption
- Consistent output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

ColorGraze QLX Powercore

Application

- Illumination of exterior facades and structures
- Illumination of moderate architectural details
- Signage and flood-/wash-lighting applications (depending on beam angle)

Versions

ColorGraze QLX Powercore BCS467
architectural lighting fixture (RGB, 305
mm)




ColorGraze QLX Powercore BCS467
architectural lighting fixture (RGB, 609
mm)



ColorGraze QLX Powercore BCS467
architectural lighting fixture (RGB,
1219 mm)



Dimensional drawing



Product	A	B
BCS467 10x60 RGB L305	134 mm	305 mm
BCS467 10x60 RGB L609	439 mm	610 mm
BCS467 30x60 RGB L1219	1049 mm	1219 mm
BCS467 10x60 RGB L1219	1049 mm	1219 mm

ColorGraze QLX Powercore

Product details



Accessories



Leader cable, 1525 mm

Ordercode 910503704064



Leader cable, 3050 mm

Ordercode 910503704067



Jumper cable, 305 mm

Ordercode 910503704077



Jumper cable, 1525 mm

Ordercode 910503704080

