



Graze EC Powercore – exterior cove, niche and detail illumination

ColorGraze EC Powercore

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features

- Soft-edged light output for volume-fill applications thanks to diffuse cover lens
- Low power consumption is perfect for less demanding exterior applications
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

Application

- Illumination of exterior coves
- Illumination of exterior details (porte-cochères, mullions, balustrades, etc.)

ColorGrazec EC Powercore

Versions

| | | | |
|---|--|--|---|
|  | ColorGrazec EC Powercore BCS468 architectural lighting fixture (RGB, 305 mm) |  | Svítidlo pro architektonické osvětlení ColorGrazec EC Powercore BCS468 (RGB, 609 mm) |
|  | Svítidlo pro architektonické osvětlení ColorGrazec EC Powercore BCS468 (RGB, 914 mm) |  | ColorGrazec EC Powercore BCS468 architectural lighting fixture (RGB, 1219 mm) |

Product details

| | | | |
|---|--|--|---|
|  | Male connector |  | Female connection |
|  | Side view of all four lengths in family |  | ColorGrazec EC Powercore 4ft ALT 1 Detail Shot |

