



# Color Graze EC Powercore – exterior cove, niche and detail illumination

## ColorGraze EC Powercore

Some exterior architectural details require a soft-edged volume fill of light. Graze EC Powercore combines this output with the proven, durable design of the Graze Powercore product family and low power consumption.

### Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

### Features

- Soft-edged light output for volume-fill applications thanks to diffuse cover lens
- Low power consumption is perfect for less demanding exterior applications
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

### Application

- Illumination of exterior coves
- Illumination of exterior details (porte-cochères, mullions, balustrades, etc.)

# ColorGraze EC Powercore

## Versions

Svitidlo pro architektonické  
osvětlení ColorGraze EC  
Powercore BCS468 (RGB, 305 mm)



Svitidlo pro architektonické  
osvětlení ColorGraze EC  
Powercore BCS468 (RGB, 1219  
mm)



## Product details

Graze MX QLX EC Connection In  
Detail photo



Graze MX QLX EC Powercore  
Connection Out Detail photo



OPDP\_BCS468i\_0005-Detail  
photo



ColorGraze EC Powercore 4ft ALT 1  
Detail Shot

