

# eW Cove MX Powercore – maximum-output linear LED fixture for cove, general and accent lighting

## eW Cove MX Powercore

With its superior light output, wide beam angle, and range of fixed colors and color temperatures, eW Cove MX Powercore can be used for accent lighting and indirect general illumination, as well as the full range of wall and ceiling cove applications. This fixture meets or exceeds the performance of comparable linear fluorescent strip cove lights while lowering installation, energy, and maintenance costs. eW Cove MX Powercore offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light. Integrated Powercore technology ensures rapid, efficient and accurate control of power output to the fixture directly from line voltage, eliminating the need for external power supplies. Use of standard wiring dramatically simplifies installation and helps lower total system cost.

### Benefits

- Maximum light output
- Multiple options for design and application flexibility
- Cost-effective, easy to install, and long lifetime

## eW Cove MX Powercore


### Features

- Fixed white or solid-color light output of up to 2000 lumens per meter; luminous efficacy of up to 53.1 lm/W
- Available in four color temperatures, ranging from a warm 2700 K to a cool 4000 K, and four solid colors (red, green, blue, and amber)
- End-to-end locking power connectors can make 180° turns; rotation in 10° increments through 170° for precise aiming and color mixing
- Smooth dimming capability with many ELV-type dimmers; guaranteed perfect dimming from 0 to 100% with Precision Dimming version
- 1200 mm version for more versatile specification and easier installation; interchangeable with 300 mm version

### Application

- Accent lighting
- Indirect general illumination

### Versions



eW Cove MX Powercore  
BCX416/421, délka 300 mm

eW Cove MX Powercore BCX416,  
délka 1200 mm

### Product details



Connection between products

Rotating mechanism

## eW Cove MX Powercore

### Product details

Create continuous lines of light



eW Cove MX Powercore BCX416  
surface-mounted LED fixture with  
leader cable

eW Cove MX 1200 mm version –  
rear view



eW Cove MX 1200 mm version –  
interchangeable with 300 mm  
version

