



ClearFlood Large – The best solution for 1:1 retrofit

ClearFlood Large

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications. It also includes all the necessary control features and interfaces to make it future-proof and even more efficient. ClearFlood Large lets you choose the exact number of lumens you need for your application. Incorporating extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution offering an outstanding lux/euro ratio and energy savings of up to 50% (without the use of additional controls). The wide choice of optics ensures maximum application coverage. ClearFlood Large is easy to install – you simply plug it in and select the best option for your needs. Perfect for replacing conventional technology and enabling intelligent lighting control while retaining the same electrical installation and poles. Tailor made solution : For tuned project solutions Philips can support with the exclusive L-Tune tool : build required flux to the best balance of life, maintained flux, energy, cost and product type.

Benefits

- Designed for 1:1 retrofit, perfect for replacing conventional technology retaining the same electrical installation and poles
- Offering a large variety of lighting needs from recreational sport, areas and even road and street, by providing a variety of optics used in the range
- Fast payback and low Total Cost of Ownership with energy savings and minimum maintenance costs
- Multiple control options ensure increased efficiency with intelligent lighting (DALI, CityTouch ready geolocalization)
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

ClearFlood Large

Features

- Designed for 1:1 retrofit up to 1000 W HID
- Wide range of lumen packages between 30 klm and 64 klm (system)
- Easy replacement of gear and PCB, no tooling required.
- Wide range of control options, such as CityTouch Ready, CLO, DALI, 1-10 V
- LEDs and optics deliver highest level of efficiency (up to 130 lm/W).
- 100% Philips components.
- Wide choice of optics to suit all applications – Sport and Areas lighting – Asymmetrical, Road and Symmetrical beams with or without louver (optional). New Asymmetrical Optic for Sport lighting (Tennis...)
- Optimized architecture for 4 kV surge (optional 10 kV).
- IP66 and IK08 protection.
- Long lifetime : 100 Khrs (L80B10 at T a 25°C)

Application

- Airports
- Harbors
- Large recreational sports facilities
- Industrial areas
- Roundabouts and motorway junctions

Specifications

| | |
|--|---|
| Type | BVP651:LEDxxx-4S BVP651i: additional options via configurator |
| Light source | Integral LED-module |
| Power | Up to 553 W (+/- 11%) all CCT |
| Luminous flux | Up to 62000 lm (NW/CW) (-/+7%) |
| Luminaire efficacy | Up to 130 lm/W (NW/CW) |
| Correlated Color | 3000, 4000 or 5700 K |
| Temperature | |
| Color Rendering Index | 80 / 70 / 70 |
| Lumen maintenance at median useful life* | up to L93 |
| 100000 h | |
| Control gear failure rate at median useful life | 10% |
| 100000 h | |
| Performance Ambient Temperature Tq | +25 °C |
| Operating temperature range | -40 to +45 °C |
| Driver | Built-in (self-ballasted LED-module) - NTC |
| Mains voltage | 220-240 V AC / 50-60 Hz |
| Power factor | >0.95 |
| Surge protection | 4 kV as standard, 10 kV as option |
| Dimming | Dimming via external communication (DALI) Dimming via mains voltage (AmpDim) Dimming via DynaDimmer (5 steps) Constant Light Output (CLO) CityTouch ready; GPRS antenna |
| Controls system input | DALI |

| | |
|------------------------|--|
| Options | Class I or II (MSP) Marine salt protection - 1000 h (SPO) Swimming Pool Protection |
| Optic | Asymmetrical, symmetrical and road optics |
| Optical element | Louver for limited backlight cut-off (BL1 and BL2) |
| Optical cover | Clear tempered flat glass |
| Material | Die-cast aluminum |
| Color | RAL9007 matt |
| Connection | Mains power via a waterproof connector (supplied) mounted on the projector and accepting cable diameters between 10 to 14 mm External control command DALI (D9), via the supplied waterproof connector (same as the mains supply) accepting cable diameters from 10 mm to 14 mm, or cable entry via 2 waterproof connectors supplied (in DALI / DALI out) |
| Maintenance | No internal cleaning required Direct access to LED engine modules and drivers Gear replacement can be asked via options Spare part list available (glass, optics, bracket, protractor scale, PCB LED, connector) |

ClearFlood Large

| | |
|---------------------|---|
| Installation | U-shaped mounting bracket with foot-print suitable for 3-point fixation by means of M20 bolts |
| | Vertical aiming from the horizontal: -90° / +90°, memory cap |
| | Standing-up or hanging-down mounting /U-bracket stirrup with standard bolts and nuts |
| | Protractor scale with intervals of 5°, memory cap |
| | Ready for CityTouch (based on DALI protocol) with external tray fixed on the bracket |

| |
|--|
| Projected area in horizontal position: at 0° 0.05 SCx: at 90° : 0.41 m², at 0° : 0.05 m², at 15° : 0.13 m² |
| Max adjustment from the horizontal: -170 to +170° |

| | |
|--------------------|---|
| Cable gland | External IP67 waterproof, plug-in connector (5-pin) |
| Remarks | CE, ENEC, RoHS, VDE-Ball proof |

Versions



Product details



Universal bracket for mounting / tilting.



Side view



Memory cap.



External connector with 5 poles IP67.

ClearFlood Large

Product details



Easy to plug in. No tooling required.



Clearflood Large CityTouch-DPP.jpg

Approval and Application

| | |
|--|--|
| Mech. impact protection code | IK08 |
| Surge Protection (Common/Differential) | Luminaire surge protection level until 4 kV differential mode and 4 kV common mode |

Controls and Dimming

| | |
|----------|----|
| Dimmable | No |
|----------|----|

General Information

| | |
|--------------------------|---|
| CE mark | CE mark |
| Light source color | 740 neutral white |
| Optical cover/lens type | Flat glass |
| Driver included | Yes |
| Flammability mark | For mounting on normally flammable surfaces |
| Light source replaceable | Yes |
| Number of gear units | 2 units |
| Product Family Code | BVP651 |

Initial Performance (IEC Compliant)

| | |
|-------------------------------|--------|
| Init. Corr. Color Temperature | 4000 K |
| Init. Color Rendering Index | ≥70 |

Light Technical

| | |
|--------------------------------|----|
| Standard tilt angle side entry | 0° |
| Standard tilt angle posttop | 0° |
| Upward light output ratio | 0 |

General Information

| Order Code | Full Product Name | Luminaire light beam spread | Lamp family code | Optic type | Service tag |
|--------------|------------------------------------|-----------------------------|------------------|--------------------------------------|-------------|
| 912300023731 | BVP651 LED450-4S/740 S ALU PSU | 70° x 21° | LED450 | Symmetrical | - |
| 912300023732 | BVP651 LED450-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED450 | Optiflux asymmetrical axis angle 52° | - |
| 912300023733 | BVP651 LED450-4S/740 DM10 ALU PSU | 157° x 111° | LED450 | Distribution medium 10 | Yes |
| 912300023734 | BVP651 LED450-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED450 | Distribution wide 10 | - |
| 912300023735 | BVP651 LED450-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED450 | Distribution extra wide 10 | - |
| 912300023736 | BVP651 LED450-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED450 | Distribution extra wide 50 | - |
| 912300023737 | BVP651 LED450-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED450 | Distribution extra wide 51 | - |
| 912300023738 | BVP651 LED500-4S/740 S ALU PSU | 70° x 21° | LED500 | Symmetrical | - |
| 912300023739 | BVP651 LED500-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED500 | Optiflux asymmetrical axis angle 52° | - |
| 912300023740 | BVP651 LED500-4S/740 DM10 ALU PSU | 157° x 111° | LED500 | Distribution medium 10 | - |
| 912300023741 | BVP651 LED500-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED500 | Distribution wide 10 | - |
| 912300023742 | BVP651 LED500-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED500 | Distribution extra wide 10 | - |
| 912300023743 | BVP651 LED500-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED500 | Distribution extra wide 50 | - |
| 912300023744 | BVP651 LED500-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED500 | Distribution extra wide 51 | - |
| 912300023745 | BVP651 LED550-4S/740 S ALU PSU | 70° x 21° | LED550 | Symmetrical | - |
| 912300023746 | BVP651 LED550-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED550 | Optiflux asymmetrical axis angle 52° | - |

| Order Code | Full Product Name | Luminaire light beam spread | Lamp family code | Optic type | Service tag |
|--------------|---------------------------------------|-----------------------------|------------------|--|-------------|
| 912300023747 | BVP651 LED550-4S/740 DM10 ALU PSU | 157° x 111° | LED550 | Distribution medium 10 | - |
| 912300023748 | BVP651 LED550-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED550 | Distribution wide 10 | - |
| 912300023749 | BVP651 LED550-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED550 | Distribution extra wide 10 | - |
| 912300023750 | BVP651 LED550-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED550 | Distribution extra wide 50 | - |
| 912300023751 | BVP651 LED550-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED550 | Distribution extra wide 51 | - |
| 912300023752 | BVP651 LED600-4S/740 S ALU PSU | 70° x 21° | LED600 | Symmetrical | - |
| 912300023753 | BVP651 LED600-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED600 | Optiflux asymmetrical axis angle 52° | - |
| 912300023754 | BVP651 LED600-4S/740 DM10 ALU PSU | 157° x 111° | LED600 | Distribution medium 10 | - |
| 912300023755 | BVP651 LED600-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED600 | Distribution wide 10 | - |
| 912300023756 | BVP651 LED600-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED600 | Distribution extra wide 10 | - |
| 912300023757 | BVP651 LED600-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED600 | Distribution extra wide 50 | - |
| 912300023758 | BVP651 LED600-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED600 | Distribution extra wide 51 | - |
| 912300023759 | BVP651 LED650-4S/740 S ALU PSU | 70° x 21° | LED650 | Symmetrical | - |
| 912300023760 | BVP651 LED650-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED650 | Optiflux asymmetrical axis angle 52° | - |
| 912300023761 | BVP651 LED650-4S/740 DM10 ALU PSU | 157° x 111° | LED650 | Distribution medium 10 | - |
| 912300023762 | BVP651 LED650-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED650 | Distribution wide 10 | - |
| 912300023763 | BVP651 LED650-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED650 | Distribution extra wide 10 | - |
| 912300023764 | BVP651 LED650-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED650 | Distribution extra wide 50 | - |
| 912300023765 | BVP651 LED650-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED650 | Distribution extra wide 51 | - |
| 912300023766 | BVP651 LED700-4S/740 S ALU PSU | 70° x 21° | LED700 | Symmetrical | - |
| 912300023767 | BVP651 LED700-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED700 | Optiflux asymmetrical axis angle 52° | - |
| 912300023768 | BVP651 LED700-4S/740 DM10 ALU PSU | 157° x 111° | LED700 | Distribution medium 10 | - |
| 912300023769 | BVP651 LED700-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED700 | Distribution wide 10 | - |

| Order Code | Full Product Name | Luminaire light beam spread | Lamp | Optic type | Service tag |
|--------------|------------------------------------|-----------------------------|-------------|--------------------------------------|-------------|
| | | | family code | | |
| 912300023770 | BVP651 LED700-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED700 | Distribution extra wide 10 | - |
| 912300023771 | BVP651 LED700-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED700 | Distribution extra wide 50 | - |
| 912300023772 | BVP651 LED700-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED700 | Distribution extra wide 51 | - |
| 912300023793 | BVP651 LED750-4S/740 S ALU PSU | 70° x 21° | LED750 | Symmetrical | - |
| 912300023794 | BVP651 LED750-4S/740 OFA52 ALU PSU | 39° - 11° x 98° | LED750 | Optiflux asymmetrical axis angle 52° | - |
| 912300023795 | BVP651 LED750-4S/740 DM10 ALU PSU | 157° x 111° | LED750 | Distribution medium 10 | - |
| 912300023796 | BVP651 LED750-4S/740 DW10 ALU PSU | 52° - 7° x 151° | LED750 | Distribution wide 10 | - |
| 912300023797 | BVP651 LED750-4S/740 DX10 ALU PSU | 20° - 4° x 150° | LED750 | Distribution extra wide 10 | - |
| 912300023798 | BVP651 LED750-4S/740 DX50 ALU PSU | 17° - 5° x 132° | LED750 | Distribution extra wide 50 | - |
| 912300023799 | BVP651 LED750-4S/740 DX51 ALU PSU | 14° - 5° x 132° | LED750 | Distribution extra wide 51 | - |
| 912300023961 | BVP651 LED450-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED450 | Distribution extra wide 60 | - |
| 912300023962 | BVP651 LED500-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED500 | Distribution extra wide 60 | - |
| 912300023963 | BVP651 LED550-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED550 | Distribution extra wide 60 | - |
| 912300023964 | BVP651 LED600-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED600 | Distribution extra wide 60 | - |
| 912300023965 | BVP651 LED650-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED650 | Distribution extra wide 60 | - |
| 912300023966 | BVP651 LED700-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED700 | Distribution extra wide 60 | - |
| 912300023967 | BVP651 LED750-4S/740 DX60 ALU PSU | 8° - 26° x 82° | LED750 | Distribution extra wide 60 | - |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial luminous flux | Order Code | Full Product Name | Initial luminous flux |
|--------------|------------------------------------|-----------------------|--------------|------------------------------------|-----------------------|
| 912300023731 | BVP651 LED450-4S/740 S ALU PSU | 39150 lm | 912300023742 | BVP651 LED500-4S/740 DX10 ALU PSU | 40500 lm |
| 912300023732 | BVP651 LED450-4S/740 OFA52 ALU PSU | 38700 lm | 912300023743 | BVP651 LED500-4S/740 DX50 ALU PSU | 41000 lm |
| 912300023733 | BVP651 LED450-4S/740 DM10 ALU PSU | 38250 lm | 912300023744 | BVP651 LED500-4S/740 DX51 ALU PSU | 25000 lm |
| 912300023734 | BVP651 LED450-4S/740 DW10 ALU PSU | 38250 lm | 912300023745 | BVP651 LED550-4S/740 S ALU PSU | 48160 lm |
| 912300023735 | BVP651 LED450-4S/740 DX10 ALU PSU | 36900 lm | 912300023746 | BVP651 LED550-4S/740 OFA52 ALU PSU | 47600 lm |
| 912300023736 | BVP651 LED450-4S/740 DX50 ALU PSU | 37350 lm | 912300023747 | BVP651 LED550-4S/740 DM10 ALU PSU | 47040 lm |
| 912300023737 | BVP651 LED450-4S/740 DX51 ALU PSU | 22500 lm | 912300023748 | BVP651 LED550-4S/740 DW10 ALU PSU | 47040 lm |
| 912300023738 | BVP651 LED500-4S/740 S ALU PSU | 43000 lm | 912300023749 | BVP651 LED550-4S/740 DX10 ALU PSU | 45360 lm |
| 912300023739 | BVP651 LED500-4S/740 OFA52 ALU PSU | 42500 lm | 912300023750 | BVP651 LED550-4S/740 DX50 ALU PSU | 45920 lm |
| 912300023740 | BVP651 LED500-4S/740 DM10 ALU PSU | 42000 lm | 912300023751 | BVP651 LED550-4S/740 DX51 ALU PSU | 28000 lm |
| 912300023741 | BVP651 LED500-4S/740 DW10 ALU PSU | 42000 lm | 912300023752 | BVP651 LED600-4S/740 S ALU PSU | 51600 lm |

ClearFlood Large

| Order Code | Full Product Name | Initial luminous flux |
|--------------|------------------------------------|-----------------------|
| 912300023753 | BVP651 LED600-4S/740 OFA52 ALU PSU | 51000 lm |
| 912300023754 | BVP651 LED600-4S/740 DM10 ALU PSU | 50400 lm |
| 912300023755 | BVP651 LED600-4S/740 DW10 ALU PSU | 50400 lm |
| 912300023756 | BVP651 LED600-4S/740 DX10 ALU PSU | 48600 lm |
| 912300023757 | BVP651 LED600-4S/740 DX50 ALU PSU | 49200 lm |
| 912300023758 | BVP651 LED600-4S/740 DX51 ALU PSU | 30000 lm |
| 912300023759 | BVP651 LED650-4S/740 S ALU PSU | 56100 lm |
| 912300023760 | BVP651 LED650-4S/740 OFA52 ALU PSU | 55440 lm |
| 912300023761 | BVP651 LED650-4S/740 DM10 ALU PSU | 54780 lm |
| 912300023762 | BVP651 LED650-4S/740 DW10 ALU PSU | 55440 lm |
| 912300023763 | BVP651 LED650-4S/740 DX10 ALU PSU | 52800 lm |
| 912300023764 | BVP651 LED650-4S/740 DX50 ALU PSU | 53460 lm |
| 912300023765 | BVP651 LED650-4S/740 DX51 ALU PSU | 32340 lm |
| 912300023766 | BVP651 LED700-4S/740 S ALU PSU | 59500 lm |
| 912300023767 | BVP651 LED700-4S/740 OFA52 ALU PSU | 58800 lm |
| 912300023768 | BVP651 LED700-4S/740 DM10 ALU PSU | 58100 lm |
| 912300023769 | BVP651 LED700-4S/740 DW10 ALU PSU | 58800 lm |

| Order Code | Full Product Name | Initial luminous flux |
|--------------|------------------------------------|-----------------------|
| 912300023770 | BVP651 LED700-4S/740 DX10 ALU PSU | 56000 lm |
| 912300023771 | BVP651 LED700-4S/740 DX50 ALU PSU | 56700 lm |
| 912300023772 | BVP651 LED700-4S/740 DX51 ALU PSU | 34300 lm |
| 912300023793 | BVP651 LED750-4S/740 S ALU PSU | 63840 lm |
| 912300023794 | BVP651 LED750-4S/740 OFA52 ALU PSU | 63080 lm |
| 912300023795 | BVP651 LED750-4S/740 DM10 ALU PSU | 62320 lm |
| 912300023796 | BVP651 LED750-4S/740 DW10 ALU PSU | 63080 lm |
| 912300023797 | BVP651 LED750-4S/740 DX10 ALU PSU | 60040 lm |
| 912300023798 | BVP651 LED750-4S/740 DX50 ALU PSU | 60800 lm |
| 912300023799 | BVP651 LED750-4S/740 DX51 ALU PSU | 37240 lm |
| 912300023961 | BVP651 LED450-4S/740 DX60 ALU PSU | 40050 lm |
| 912300023962 | BVP651 LED500-4S/740 DX60 ALU PSU | 44000 lm |
| 912300023963 | BVP651 LED550-4S/740 DX60 ALU PSU | 49280 lm |
| 912300023964 | BVP651 LED600-4S/740 DX60 ALU PSU | 52800 lm |
| 912300023965 | BVP651 LED650-4S/740 DX60 ALU PSU | 58080 lm |
| 912300023966 | BVP651 LED700-4S/740 DX60 ALU PSU | 61600 lm |
| 912300023967 | BVP651 LED750-4S/740 DX60 ALU PSU | 66120 lm |

Mechanical and Housing

| Order Code | Full Product Name | Color |
|--------------|------------------------------------|-------|
| 912300023731 | BVP651 LED450-4S/740 S ALU PSU | Gray |
| 912300023732 | BVP651 LED450-4S/740 OFA52 ALU PSU | Gray |
| 912300023733 | BVP651 LED450-4S/740 DM10 ALU PSU | Gray |
| 912300023734 | BVP651 LED450-4S/740 DW10 ALU PSU | Gray |
| 912300023735 | BVP651 LED450-4S/740 DX10 ALU PSU | Gray |
| 912300023736 | BVP651 LED450-4S/740 DX50 ALU PSU | Gray |
| 912300023737 | BVP651 LED450-4S/740 DX51 ALU PSU | Gray |
| 912300023738 | BVP651 LED500-4S/740 S ALU PSU | Gray |
| 912300023739 | BVP651 LED500-4S/740 OFA52 ALU PSU | Gray |
| 912300023740 | BVP651 LED500-4S/740 DM10 ALU PSU | Gray |
| 912300023741 | BVP651 LED500-4S/740 DW10 ALU PSU | Gray |
| 912300023742 | BVP651 LED500-4S/740 DX10 ALU PSU | Gray |
| 912300023743 | BVP651 LED500-4S/740 DX50 ALU PSU | Gray |
| 912300023744 | BVP651 LED500-4S/740 DX51 ALU PSU | Gray |
| 912300023745 | BVP651 LED550-4S/740 S ALU PSU | Gray |
| 912300023746 | BVP651 LED550-4S/740 OFA52 ALU PSU | Gray |
| 912300023747 | BVP651 LED550-4S/740 DM10 ALU PSU | Gray |
| 912300023748 | BVP651 LED550-4S/740 DW10 ALU PSU | Gray |
| 912300023749 | BVP651 LED550-4S/740 DX10 ALU PSU | Gray |
| 912300023750 | BVP651 LED550-4S/740 DX50 ALU PSU | Gray |
| 912300023751 | BVP651 LED550-4S/740 DX51 ALU PSU | Gray |
| 912300023752 | BVP651 LED600-4S/740 S ALU PSU | Gray |
| 912300023753 | BVP651 LED600-4S/740 OFA52 ALU PSU | Gray |
| 912300023754 | BVP651 LED600-4S/740 DM10 ALU PSU | Gray |
| 912300023755 | BVP651 LED600-4S/740 DW10 ALU PSU | Gray |
| 912300023756 | BVP651 LED600-4S/740 DX10 ALU PSU | Gray |
| 912300023757 | BVP651 LED600-4S/740 DX50 ALU PSU | Gray |
| 912300023758 | BVP651 LED600-4S/740 DX51 ALU PSU | Gray |

| Order Code | Full Product Name | Color |
|--------------|------------------------------------|----------|
| 912300023759 | BVP651 LED650-4S/740 S ALU PSU | Gray |
| 912300023760 | BVP651 LED650-4S/740 OFA52 ALU PSU | Gray |
| 912300023761 | BVP651 LED650-4S/740 DM10 ALU PSU | Gray |
| 912300023762 | BVP651 LED650-4S/740 DW10 ALU PSU | Gray |
| 912300023763 | BVP651 LED650-4S/740 DX10 ALU PSU | Gray |
| 912300023764 | BVP651 LED650-4S/740 DX50 ALU PSU | Gray |
| 912300023765 | BVP651 LED650-4S/740 DX51 ALU PSU | Gray |
| 912300023766 | BVP651 LED700-4S/740 S ALU PSU | Gray |
| 912300023767 | BVP651 LED700-4S/740 OFA52 ALU PSU | Gray |
| 912300023768 | BVP651 LED700-4S/740 DM10 ALU PSU | Gray |
| 912300023769 | BVP651 LED700-4S/740 DW10 ALU PSU | Gray |
| 912300023770 | BVP651 LED700-4S/740 DX10 ALU PSU | Gray |
| 912300023771 | BVP651 LED700-4S/740 DX50 ALU PSU | Gray |
| 912300023772 | BVP651 LED700-4S/740 DX51 ALU PSU | Gray |
| 912300023793 | BVP651 LED750-4S/740 S ALU PSU | Gray |
| 912300023794 | BVP651 LED750-4S/740 OFA52 ALU PSU | Gray |
| 912300023795 | BVP651 LED750-4S/740 DM10 ALU PSU | Gray |
| 912300023796 | BVP651 LED750-4S/740 DW10 ALU PSU | Gray |
| 912300023797 | BVP651 LED750-4S/740 DX10 ALU PSU | Gray |
| 912300023798 | BVP651 LED750-4S/740 DX50 ALU PSU | Aluminum |
| 912300023799 | BVP651 LED750-4S/740 DX51 ALU PSU | Gray |
| 912300023961 | BVP651 LED450-4S/740 DX60 ALU PSU | Gray |
| 912300023962 | BVP651 LED500-4S/740 DX60 ALU PSU | Gray |
| 912300023963 | BVP651 LED550-4S/740 DX60 ALU PSU | Gray |
| 912300023964 | BVP651 LED600-4S/740 DX60 ALU PSU | Gray |
| 912300023965 | BVP651 LED650-4S/740 DX60 ALU PSU | Gray |
| 912300023966 | BVP651 LED700-4S/740 DX60 ALU PSU | Gray |
| 912300023967 | BVP651 LED750-4S/740 DX60 ALU PSU | Gray |

ClearFlood Large

