



Classic look & feel and LED filament for decorative lighting

Classic frosted LED Lamps

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Benefits

- Around 90% energy saving
- Long lifetime reduces need for replacement
- Environmentally friendly: contains no mercury or other hazardous substances

Features

- Heritage design with classic shape
- Long LED Filament

Application

- Home: living room, bedroom
- Hospitality: restaurants and hotels

Classic frosted LED Lamps

Versions




LED Lamps, LEDclassic A60 E27
WW FR



Bulb A67 100W 1521lm 2700K E27
NDFrosted

Dimensional drawing



Product	D	C
LED classic 40W A60 E27 WW FR ND 1CT/10	60 mm	110 mm
LED classic 60W A60 E27 WW FR ND 1CT/10	60 mm	110 mm

Classic frosted LED Lamps

General Information

Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	30,000
Nominal lifetime	15,000 hour(s)

Light Technical

Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
Color Code	827
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	50 Hz
Line Frequency	50 Hz
Starting Time (Nom)	0.5 s

Temperature

T-Case Maximum (Nom)	50 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A60

Light Technical

Order Code	Full Product Name	Luminous Flux
47218701	LED classic 60W A60 E27 WW FR ND 1CT/10	806 lm
41965601	LED classic 40W A60 E27 WW FR ND 1CT/10	470 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
47218701	LED classic 60W A60 E27 WW FR ND 1CT/10	7 W

Order Code	Full Product Name	Power Consumption
41965601	LED classic 40W A60 E27 WW FR ND 1CT/10	4.5 W


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
47218701	LED classic 60W A60 E27 WW FR ND 1CT/10	7 kWh
41965601	LED classic 40W A60 E27 WW FR ND 1CT/10	5 kWh

Classic frosted LED Lamps

120°

90°



Classic frosted LED Lamps

