



IntelliHue SkyRibbon Wall Washing Powercore

SkyRibbon IntelliHue Wall Washing Powercore

Introducing SkyRibbon IntelliHue Wall Washing Powercore, a recessed linear interior LED wall-washing fixture offering high-quality intelligent colour and white light from the same fixture. IntelliHue is an advanced approach to colour mixing that enables users to precisely target a full spectrum of saturated colour and high-quality white light, granting an unprecedented level of design freedom. Brilliant light output and industry-leading controls make this fixture ideal for a variety of interior wall-washing applications. Users can rotate the LED modules from 0° to 90° to evenly wash walls top to bottom regardless of fixture setback. Multiple housing options accommodate a number of installation methods.

Benefits

- Mimics all shades of white
- Precise colour changing
- Dynamic recessed accent-lighting fixture

Features

- Unique IntelliHue technology enables high-quality intelligent colour and white light from the same fixture
- Consistent colour from fixture to fixture
- No hot-spotting, colour shifting, tiger-striping, or unwanted edge effects
- Tunable white – precise control of colour temperature
- Free from beam striations – high-quality white light

Application

- Hospitality
- Fashion
- Office

Specifications

SkyRibbon IntelliHue Wall Washing Powercore


Type	RA503S
Ceiling type	T-Bar ceiling Slot-T ceiling Flangeless Plasterboard ceiling
Ceiling grid	Module size in length: 600 mm
Light source	Replaceable LED module
Power	66 W
Beam angle	20 x 20°, 30 x 30°, 30 x 60°, 35 x 105°, 40 x 80°, 65 x 65°, 70 x 95° or 90 x 90°
Luminous flux	1451 lm (RGB only), 2315 lm (2700 K), 2867 lm (4000 K) with 20 x 20° lens
Maintenance of lumen output - L70F50	60,000 hours at 25 °C
Operating temperature range	-20 to +40 °C

Driver	Built-in
Power/Data supply	Data enabler Pro; integrated data and power for intelligent LED lighting fixtures using Powercore
Mains voltage	120 VAC, 220 to 240 VAC, and 277 VAC / 50-60 Hz
Dimming	Digital dimmer
Controls system input	DMX, Ethernet
Options	Holographic Diffusion lens accessory
Material	Housing: steel, white powder-coated finish Lens: polycarbonate
Colour	White (WH)
Optic	Polycarbonate lens, clear
Connection	Wieland integral male / female connectors
Installation	Recessed in the ceiling Through-wiring possible

Versions



Product details



SkyRibbon IntelliHue Wall Washing Powercore

Product details



Accessories



Ordercode 910503702690,
910503704249



Ordercode 910503704213,
910503704214, 910503704215,
910503704216, 910503704218,
910503704219, 910503704220



Ordercode 61826300



Ordercode 910503705049,
910503705050, 910503705051

