



iColor MR gen3 – intelligent RGB MR16 LED lamp for intense, saturated bursts of color

iColor MR gen3

iColor MR gen3 is an intelligent color-changing lamp that delivers intense, saturated bursts of color and color-changing effects. The stylish housing fits into most standard MR16 fixtures, including tracks, cables, rails, and pendants. With high-intensity LED light sources and three beam angles, iColor MR gen3 is suitable for a wide range of architectural, theatrical, and retail applications.

Faydaları

- High-quality light output, superior output consistency; less commissioning time required
- Light output can be tailored to the application
- Simple installation and control with standard two-conductor cable or hook-up wire

Özellikler

- Can be used with most standard MR16 bi-pin base fixtures – track heads, pendants, chandeliers, sconces, pinspots, striplights
- Narrow, medium and wide beam angles to tailor light output for flood, spot, wash and direct-view applications
- Simple installation with standard two-conductor cable
- Individual unit control via PDS-70mr 24V power/data supply – from simple, preprogrammed effects to DMX/Ethernet control

iColor MR gen3

Uygulama

- Retail
- Hospitality
- Entertainment
- Direct view

Versions



RGB zdroj iColor MR g3 RS500S s
vyzařovacím úhlem 17°

