



# StyliD PremiumWhite

## – Ideal mix of outstanding light quality and energy savings for (fashion) retailers

### StyliD PremiumWhite

If you want a high quality of light and color rendering for your store, without having to compromise on energy savings, then StyliD PremiumWhite is exactly what you are looking for. This exciting solution delivers the same sparkling light effects as CDM conventional lighting. So now you can make the switch to LED with confidence!

#### Benefits

- Natural, warm light delivering outstanding colors and whites
- Very good efficiency (>85 lm/W)

#### Features

- CRI >90
- PerfectAccent reflectors
- Light efficacy on par with CCT 930
- SDCM3
- Light color positioning below black body locus (similar to CDM)

#### Application

- Fashion and furniture stores
- Hospitality areas (hotels)

# StyliD PremiumWhite

## Specifications


<b>Type</b>	ST740T (compact, 3C-track version)
	ST740C (compact, surface-mounted version)
<b>Light source</b>	Replaceable LED module
<b>Power</b>	18.5 W (LED17S)
	30.5 W (LED27S)
<b>Beam angle</b>	MB: 24° (LED17S), 29° (LED27S)
	WB: 36° (LED17S), 35° (LED27S)
	MB LIN (MB + oval lens): 41 x 28° (LED17S), 40 x 36° (LED27S)
	WB LIN (WB + oval lens): 53 x 33° (LED17S), 42 x 36° (LED27S)
<b>Luminous flux</b>	1,800 or 2,800 lm
<b>Light source colour</b>	Premium white with CRI>90 (PW9)
<b>Correlated Colour</b>	3,000 K
<b>Temperature</b>	
<b>Colour Rendering Index</b>	> 90
<b>Lumen maintenance at median useful life*</b>	L80
<b>50,000 h</b>	
<b>Control gear failure rate at median useful life</b>	5%
<b>50,000 h</b>	

<b>Performance Ambient</b>	+25 °C
<b>Temperature Tq</b>	
<b>Operating temperature range</b>	+10 to +35 °C
<b>Driver</b>	Built-in
<b>Mains voltage</b>	230 or 240 V/50-60 Hz
<b>Material</b>	Gearbox: plastic
	Head and heatsink: die-cast aluminium
	Front cover: acrylic or glass
<b>Colour</b>	Black (BK, RAL9004)
	White (WH, RAL9003)
	White-Black (WH-BK, RAL9003-RAL9004)
	Aluminium brushed-black (ALU-BK, ALU-RAL9004)
	Silver-black (SI-BK, RAL9006-RAL9004)
<b>Optical cover</b>	Clear with jaws (for medium beam)
	Clear with diffusor foil (for other beams)
<b>Connection</b>	3C track connector or DALI connector
<b>Installation</b>	On 3-circuit track
	Individual; screw mounting

## Versions



## Product details



## StyliD PremiumWhite

### Product details

