



Create flexible shop ambiances for selling

StoreSet

Today's retail destinations are all about creating experiences that attract and retain customers. StoreSet adds atmosphere to your store by introducing contrast and breaking up the traditional continuous lines of light. A variety of beam shapes, combined with excellent light quality, ensures that your merchandise stands out, at the same time as enabling you to create a variety of different ambiances. Each StoreSet panel is lightweight and can be easily connected to power tracks or a Maxos fusion backbone. Installation is straightforward, and if your needs change, you can simply adapt the lighting by repositioning the panels and luminaires along the track or trunk. This makes StoreSet a truly flexible, non-linear tool for creating store ambiances that sell.

Benefits

- Customised store ambiance with a high-flux luminaire and flexible positioning to suit any store layout
- Excellent quality of light combined with high efficiency enabled by the wide range of optics and various colour recipes
- Future-proof solution accommodating future initiatives related to store layout or system enhancement

Features

- Wide range of beams and optics available
- Track connection (3C track or Maxos fusion trunking) or recessed
- Efficient solution: up to 170 lumens per watt (XA version)
- Easy to install and connect, lightweight
- Project specifications available; DALI, emergency lighting, CLO-enabled, indoor positioning and Interact Pro connected system
- Colour quality choices: CRI80, CRI90, Premium White

Application

- Food and large retailers
- Retail

Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

