



# Circular shaped, basic fluorescent lighting

## TL-E LIFEMAX Standard Colours JIS

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important. The lamp complies with the Japanese Industrial Standard.

### Benefits

- Standard colours with moderate colour rendering (R a 50 - 70)
- Create atmospheres from warm white to cool daylight

### Features

- Available in varying colour designations
- Symmetrical, omni-directional light distribution

### Application

- Standard colours with moderate colour rendering (R a 50 - 70)
- Create atmospheres from warm white to cool daylight