



# ColorBlast RGB Powercore gen4 – Customisable exterior LED flood luminaire with intelligent colour light

## ColorBlast Powercore gen4 RGB

ColorBlast Powercore gen4 high-performance LED luminaires combine white and rich, saturated, colour and colour-changing effects with simplified installation. ColorBlast Powercore gen4 offers a range of accessories that allow for customisable beam angles for floodlighting, spotlighting, wall washing and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

### Benefits

- Higher lumen output for a dynamic colour luminaire
- Colour flexibility and consistency
- Complete set of accessories

# ColorBlast Powercore gen4 RGB

## Features

- Expands customisation with a wide range of new accessory options. In addition to the native 10° lens, five different diffuser lenses can customise the fixture to produce 20°, 40°, 60° and 80°, and 10° x 40° (asymmetric), beam angles. Three housing colour choices (black, grey and white) – plus the option to add or combine a louvre, rock guard, full-glare shield and half-glare shield – create new aesthetic possibilities for designers and architects.
- Improves colour consistency between all LED luminaires in a family with Chromasync technology. During the manufacturing process a calibrated light measurement device creates an algorithm to define a common colour gamut for an entire family of LED fixtures. When Chromasync is enabled, colour consistency between luminaires is achieved without having to manually adjust colour points on each fixture.
- Features an innovative, redesigned optical system that improves the quality of light from each LED, enhancing the colour uniformity and colour mixing capabilities of each ColorBlast Powercore gen4 luminaire.
- Improves durability with new flat lens that prevents water from pooling into the luminaire, keeping the LEDs protected and secure over the course of a luminaire's lifetime.
- Integrates patented Powercore technology that controls power output to luminaires directly from line voltage – rapidly, efficiently and accurately. The Color Kinetics Data Enabler Pro merges line voltage with control data and delivers them to fixtures over a single standard cable, dramatically simplifying installation and lowering total system cost.

## Application

- Buildings facades
- Monuments and sculptures
- Parks and gardens
- Bridges and structures

## Versions



## ColorBlast Powercore gen4 RGB

### Product details

Blast Powercore gen4/gen5, RGBA  
four channel LED fixture back view



Blast Powercore gen4/gen5, RGBA  
four channel LED fixture front view



Blast Powercore gen4/gen5, RGBA  
four channel LED fixture side view

