



ColorBlast IntelliHue Powercore gen4 - high-quality tunable white light

ColorBlast IntelliHue Powercore gen4

ColorBlast IntelliHue Powercore gen4 combines precision color control with high-quality tunable white light in one outdoor luminaire for wall-washing and spotlighting applications. IntelliHue, an advanced approach to color control and mixing, produces an enhanced spectrum of precisely controllable light, including millions of saturated colors, pastels, and precisely controllable, high-quality white and tinted white light. By combining carefully selected channels of LED light sources, IntelliHue enables high-quality intelligent color and white light from the same fixture. The fixture's completely flat front lens creates a minimalist, clean design and prevents any water pooling or debris accumulation, so the light is never interrupted. There is a full set of accessories that can be used in combination or alone, including a full-height glare shield, half-glare shield, louver, rock guard, and diffusers to alter the beam from 10° up to 80°.

Benefits

- Higher color rendering for façade lighting
- Color flexibility and consistency
- Complete set of accessories

ColorBlast IntelliHue Powercore gen4

Features

- Powercore technology directly accepts line voltage
- Optional spread lenses of 20°, 40°, 60°, 80°, and 10° x 40° asymmetric
- High-quality tunable white and colored light in the same fixture, enabling tinting of any color temperature between 2000 and 10,000 K above and below the black-body curve
- Light output of 200–1500 lumens at CRI of >80 in the 2700–4000 K range
- Superior color consistency and accuracy with OptiBin and Chromasync technologies

Application

- Building facades
- Monuments and sculptures
- Parks and gardens
- Bridges and structures

Versions

Přisazené LED svítidlo ColorBlast
IntelliHue gen4 Powercore
BCP483



ColorBlast IntelliHue Powercore gen4

Product details



OPDP_BCP480i_0013-Detail
photo



OPDP_BCP480i_0015-Detail
photo



Blast IntelliHue Powercore gen4
surface-mounted LED fixture front
view

