



# Product Description

## Plusline Large

Mains-voltage linear lamp giving white halogen light

### Benefits

- Bright halogen light
- Long lifetime of 2000 hours

### Features

- Clear tubular quartz bulb
- Constant light output during life
- Colour temperature 2900K
- Excellent colour rendering (R a = 100)
- Limited burning position:  $\pm 4^\circ$

### Application


- Typically used in outdoor applications: billboards, car parks, security lighting and construction sites
- Also used in Indoor applications: homes, offices, shops and museums

### Versions



Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 240V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

